



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ICN4P32N35M 4LMP F32T8 120-277V Elec Bal

*Advance By Signify*

|                  |   |
|------------------|---|
| Catalog Number   | ICN4P32N35M   |
| Manufacturer     | Advance By Signify  |
| Description      | The Right Choice For A Broad Range Of New Construction and Retrofit Applications Compatible With Energy Saving Lamps;Eligible For Utility Rebates;Maximizes Fixture Design;Reduces Packaging Waste Reliable and Energy Efficient Philips Advance'S Centium Commercial Grade Specifications, Plus Added Benefits Of Lamp Striation Reduction Technology. Intellivolt (120-277V) Input Voltage Range;Lamp Striation Reduction;Meets Nema Premium/Cee;Smallest Enclosure In Industry General Office Lighting, Institutional, Gover |
| Weight per unit  | 0.8800 (lbs/each)   |
| Product Category | Electronic Linear Fluorescent   |

### Features

|                              |              |
|------------------------------|--------------|
| amperage rating              | 0.94-0.41    |
| ANSI Code                    | N/A          |
| Ballast Factor               | 0.88         |
| dimnable                     | Non Dimmable |
| Lamp Type                    | Fluorescent  |
| Minimum Starting Temperature | -20          |
| Number of Lamps              | 4            |
| Power Factor                 | 0.98         |
| start type                   | Instant      |
| total harmonic distortion    | <=10         |
| Voltage Rating               | 120-277      |
| Wattage                      | 112          |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | Black |
|-------|-------|

### Dimensions and Weight

|        |      |
|--------|------|
| Height | 3.94 |
| Length | 3.74 |
| Width  | 5.12 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | 4LMP F32T8 120-277V ELEC BAL  |
| extra long description | ADV 109140 ELE BALLAST (4) F32T8 12   |
| Long Description       | The right choice for a broad range of new construction and retrofit applications Compatible with Energy Saving lamps;Eligible for Utility Rebates;Maximizes fixture design;Reduces packaging waste Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology. IntelliVolt (120-277V) input voltage range;Lamp Striation Reduction;Meets NEMA Premium/CEE;Smallest enclosure in industry General office lighting, institutional, gover |
| Product Type           | Ele Ballast (4) F32T8 120-277V  |
| Special Features       | IntelliVolt 120-277V, Parallel Lamp Operation   |

## Manufacturer Information

|                           |                     |
|---------------------------|---------------------|
| Brand                     | Signify Electronics |
| GTIN                      | 00781087091524      |
| Manufacturers Part Number | ICN4P32N35M         |
| UPC                       | 781087091524        |

## Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | ELECTRONIC BALLAST |
| Type                 | ELECTRONIC         |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 30   |
| Weight Per each | 0.88 |

## Uses, Certifications, and Standards

|                  |  |
|------------------|--|
| Application      | Commercial   |
| Frequency Rating | 50to60   |
| Mounting         | 8.9  |
| standard         | CSA certificate;UL certificate;CEC Listing;CEE Rated;NEMA Premium;NOM certificate;RoHS Compliant |