

INSULATING GLOVES

JOB SAFETY FITS LIKE A GLOVE.

CLASS 00

Low Voltage
500V Max



CLASS 0

Low Voltage
1000V Max



CLASS 1

High Voltage
7500V Max



CLASS 2

High Voltage
17500V Max



Insulating rubber gloves are the first line of protection against electrical shock. Class 00, 0, 1 and 2 gloves are available in a full range of sizes to comfortably fit most employees. In accordance with OSHA Standard 1910.137(b)(2)(xii) Cementex Certifies that all gloves are dielectrically tested at time of sale. OSHA also requires gloves be dielectrically tested every 6 months.

GLOVE KITS CONSIST OF PROTECTORS, GLOVES AND CARRY BAG.



Also, available are Glove Inflators, Cotton Liners, Talc and Dielectric Testing and Retesting Service.

Daily use of a Cementex Glove Inflator will keep you in compliance with OSHA 1910.137 which states, in part, . . . "Insulating equipment shall be inspected before each day's use and immediately following an incident that can reasonably be suspected of having caused damage. Insulating gloves shall be given an air test, along with the inspection."



• CHECK OUR ILLUSTRATED PRICE LIST FOR DETAILS

Gloves

Glove color may vary and is at our discretion unless certain color is specified at time of order. Color selection may impact product delivery timeframe.



Rubber Insulating Class 00 Gloves

Low Voltage Gloves -- 500V Max, ASTM Spec, Tested & Certified

Size	Glove (11" Long)	Protector (10" Long)	Glove Kit (Glove, Protector & Storage Bag)
8	IG00-11-8 \$53.00	P00-10-8 \$16.00	IGK00-11-8 \$86.00
9	IG00-11-9 \$53.00	P00-10-9 \$16.00	IGK00-11-9 \$86.00
10	IG00-11-10 \$53.00	P00-10-10 \$16.00	IGK00-11-10 \$86.00
11	IG00-11-11 \$53.00	P00-10-11 \$16.00	IGK00-11-11 \$86.00
12	IG00-11-12 \$53.00	P00-10-12 \$16.00	IGK00-11-12 \$86.00

Rubber Insulating Class 0 Gloves

Low Voltage Gloves -- 1000V Max, ASTM Spec, Tested & Certified

Size	Glove (11" Long)	Protector (10" Long)	Glove Kit (Glove, Protector & Storage Bag)
8	IG0-11-8 \$56.00	P0-10-8 \$17.00	IGK0-11-8 \$89.00
9	IG0-11-9 \$56.00	P0-10-9 \$17.00	IGK0-11-9 \$89.00
10	IG0-11-10 \$56.00	P0-10-10 \$17.00	IGK0-11-10 \$89.00
11	IG0-11-11 \$56.00	P0-10-11 \$17.00	IGK0-11-11 \$89.00
12	IG0-11-12 \$56.00	P0-10-12 \$17.00	IGK0-11-12 \$89.00

Rubber Insulating Class 2 Gloves

High Voltage Gloves -- 17kV Max, ASTM Spec, Tested & Certified

Size	Glove (14" Long)	Protector (12" Long)	Glove Kit (Glove, Protector & Storage Bag)
8	IG2-14-8 \$98.00	P2-12-8 \$24.00	IGK2-14-8 \$135.00
9	IG2-14-9 \$98.00	P2-12-9 \$24.00	IGK2-14-9 \$135.00
10	IG2-14-10 \$98.00	P2-12-10 \$24.00	IGK2-14-10 \$135.00
11	IG2-14-11 \$98.00	P2-12-11 \$24.00	IGK2-14-11 \$135.00
12	IG2-14-12 \$98.00	P2-12-12 \$24.00	IGK2-14-12 \$135.00



NOTE: Additional Classes and Lengths available upon request. Special orders may have potentially long lead times.

Thermographers Gloves

40 Calorie: Size Regular	GT40R	\$82.00
40 Calorie: Size Large	GT40L	\$88.00
65 Calorie: Size Regular	GT65R	\$88.00
65 Calorie: Size Large	GT65L	\$92.00
100 Calorie: Size Regular	GT100R	\$98.00



Glove Accessories

Type	Description	Part Number	Price
Canvas Glove Storage Bags			
	Canvas Glove Storage Bag: 12", Single Snap Closure	CGB12	\$20.00
	Canvas Glove Storage Bag: 16", Double Snap Closure	CGB16	\$24.50
	Canvas Glove Storage Bag: 20", Double Snap Closure	CGB20	\$28.00
Glove Inflator			
	<p>Glove Inflator</p> <p>New easy-to-use design features non-slip base and doesn't require straps or bands for fast visual inspections.</p>	CPGI	\$88.00
Glove Talc & Cleaner			
	Talc: 6 Oz. Squirt Bottle	CPGT-6SB	\$8.50
	Talc: Case of 6 Oz. Squirt Bottles (12 each)	CPGT-12CB	\$85.00
	Talc: 1 Qt. Container	CPGT-1QC	\$28.00
	Talc: Case of 1 Qt. Containers (4 each)	CPGT-4QC	\$110.00
	Talc: 1 Gallon Container	CPGT-1GC	\$58.00
	Liquid Cleaner: 1 Gallon Container	CP1GC	\$63.00
Glove Liners			
	Cotton Glove Liner: 10" Length	COTGLV10	\$4.20
	Cotton Glove Liner: 12" Length	COTGLV12	\$4.20
	Wool Glove Liner: 10" Length	WOLGLV10	\$5.10