



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG5261 Recp SGL 15A 125V S+B Wire Ig

Pass & Seymour/Legrand

| | |
|------------------|-------------------------------------------------------------------------------------|
| Catalog Number | IG5261 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Isolated Ground Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V |
| Weight per unit | 0.1704 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--------------------------------------------------|
| amperage rating | 15 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| Material | Nylon |
| media | Yes |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Orange |
|-------|--------|

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.68 |
| Width | 1.093 |

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | RECP SGL 15A 125V S+B WIRE IG |
| extra long description | P&S IG5261 RECEPT SINGLE 15A 125V S |
| Long Description | Isolated Ground Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V |
| Product Type | Recept Single 15A 125V S+B Wire Ig |
| Special Features | IG symbol and Isolated Ground markings for easy identification and circuit delineation. Triple-wipe brass contacts ensure lasting, positive contact with plug blades. High-impact resistant nylon face resists impacts and scrapes. Corrosion-resistant plated steel strap. Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Side and internal screw-pressure-plate back wi |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007652611 |
| Manufacturers Part Number | IG5261 |
| UPC | 785007652611 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------------------------------------|
| Category Description | Commercial receptacles |
| Type | Isolated Ground Spec Grade Single Receptacle, Heavy-Duty |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.1704 |

Uses, Certifications, and Standards

| | |
|--------------------------|---------------------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-15R |
| standard | CUL, UL498, CSA C22.2 No. 42, FEDSPEC |
| Temperature Rating | -40° - 60° C |