



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IGL520R Turnlok Recp SGL 3W 20A 125V Ig

Pass & Seymour/Legrand

Catalog Number	IGL520R
Manufacturer	Pass & Seymour/Legrand
Description	Turnlok Registered Receptacle Single 3-Wire 20A 125V Isolated Ground
Weight per unit	0.2200 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
indoor/outdoor	Indoor
Number of Wires	3
Outlet Type	Isolated Ground
Phase	3
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	TURNLOK RECP SGL 3W 20A 125V IG
extra long description	P&S IGL520R TURNLOK RECEPT SGL 3W 2
Features	Brass Mounting Strap
Long Description	Turnlok Registered Receptacle Single 3-Wire 20A 125V Isolated Ground
Product Type	Turnlok Recept SGL 3W 20A 125V Ig
Special Features	Corrosion resistant turnlock locking device

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007252354
Manufacturers Part Number	IGL520-R
UPC	785007252354

Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	Outlet



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
--------	---

Package	50
---------	----

Weight Per each	0.22
-----------------	------

Uses, Certifications, and Standards

Application	Industrial
-------------	------------

nema rating	L5-20R
-------------	--------

Operating Temperature	-40°-75°C
-----------------------	-----------

standard	FEDSPEC, CULUS, UL 498, FEDSPEC
----------	---------------------------------