



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **IPLD25010 250MCM-6AWG 10PRT, 2SD Insld Multi Tap** *Nsi Industries*

Catalog Number	IPLD25010
Manufacturer	Nsi Industries
Description	The Polaris IPLD250-10 Multi-Tap Dual-Sided Entry Connector Features 10 Ports Sized For 250 MCM - 6 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Tra
Weight per unit	1.2 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Material	Aluminum
Number of Conductors	10
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	250 MCM-6 AWG
Wire Type	Class B & C

### **Material, Color, and Finish**

Color	Black
Finish	Plastisol Insulated

### **Dimensions and Weight**

Size	L=8.970 - W=2.280 - H=2.180
------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	250MCM-6AWG 10PRT,2SD INSLTD MULTI TAP
extra long description	NSI IPLD250-10 POLARIS Ins Multi-Ta
Features	The Polaris IPLD250-10 10-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to ten conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 250 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric str
Long Description	The Polaris IPLD250-10 Multi-Tap Dual-Sided Entry Connector features 10 ports sized for 250 MCM - 6 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable tra
Product Type	Polaris Ins Multi-Tap 250 4 Port Dse
Special Features	(10) 250 MCM-6 AWG - Dual Rated

## Manufacturer Information

Brand	Polaris
GTIN	00662381923080
Manufacturers Part Number	IPLD250-10
UPC	662381923080

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Double Sided Entry

## Packaging

Carton	2
Weight Per each	1.1599

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C