



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390



IPLD2508 250-6 2S 8 Multi Cable Insul Tap

Nsi Industries

Catalog Number	IPLD2508
Manufacturer	Nsi Industries
Description	The Polaris IPLD250-8 Multi-Tap Dual-Sided Entry Black Connector Features 8 Ports Sized For 250 MCM - 6 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable
Weight per unit	0.9300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Number of Conductors	8
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	250 MCM-6 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated
Housing Material	Aluminum

Dimensions and Weight

Size	L=7.240 - W=2.280 - H=2.180
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390

Descriptions

Description	250-6 2S 8 MULTI CABLE INSUL TAP
extra long description	NSI IPLD250-8 250 Mcm - 6 Awg Polar
Features	The Polaris IPLD250-8 8-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to eight conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 250 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric str
Long Description	The Polaris IPLD250-8 Multi-Tap Dual-Sided Entry Black Connector features 8 ports sized for 250 MCM - 6 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable
Product Type	250 MCM - 6 Awg Polaris Insulated Multi-Tap Conn 8 Port (Dua
Special Features	(8) 250 MCM-6 AWG - Dual Rated

Manufacturer Information

Brand	Polaris
GTIN	00662381923066
Manufacturers Part Number	IPLD250-8
UPC	662381923066

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Double Sided Entry

Packaging

Carton	3
Weight Per each	0.93

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B