



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IPLD303 3/0-#6 3 Pole Polaris Connector Block

Nsi Industries

Catalog Number	IPLD303
Manufacturer	Nsi Industries
Description	Multi-Tap Connector, #6 Awg Conductor Size, 3/0 Awg Conductor Size, Insulated, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, 3 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 2.63 In Overall Length, 600 V, 0.31 LB/Ea
Weight per unit	0.3100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	3/0-6 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

Dimensions and Weight

Size	L=2.630 - W=1.830 - H=1.790
------	-----------------------------

Descriptions

Description	3/0-#6 3 POLE POLARIS CONNECTOR BLOCK
extra long description	NSI IPLD3/0-3 POLARIS Ins Multi-Tap
Features	The Polaris IPLD3/0-3 3-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to three conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 3/0 - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strengt

Manufacturer Information

GTIN	00662381927019
UPC	662381927019



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Double Sided Entry

Packaging

Carton	6
Weight Per each	0.31

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C