



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2646 SE Washington Blvd
74006-0000, OK Bartlesville
Phone: 918-876-3357
Fax: 918-876-3358



IR07 Dual Ir/Probe Thermometer

Klein Tools

Catalog Number	IR07
Manufacturer	Klein Tools
Description	The Klein Tools IR07 Is A Dual Ir (Infrared) Thermometer and Probe Thermometer. This Rugged Pocket Thermometer Measures Temperature From -40 to 572-Degrees Fahrenheit (-40 to 400-Degrees Celsius) For Both Ir and Probe Measurements. The Ir Thermometer Has A Distance-to-Spot Ratio Of 8:1 and The Target Laser Can Also Be Used As A Laser Pointer. The Probe Accurately Measures Air, Liquid and Surface Temps and Has A Convenient Hook For Hands Free Indoor Measurements. The IR07 Quickly Calculates Differential Tem
Weight per unit	0.0870 (lbs/each)
Product Category	Meters, Panel Instruments

Features

Accuracy	-40 to 0° C: +/-2°; 1 to 300° C: +/- 1°C
display	Backlit LCD
included	IR07 Dual IR and Probe Thermometer; Pouch; Owner's Manual and 2 x AAA Batteries
Material	ABS, Polycarbonate
media	Yes
Overall Height	0.95" (2.4 cm)
Overall Width	1.67" (4.2 cm)
Range	-40° to 572° F (-40° to 300° C)
Response Time	IR <500 ms; Probe <20 s

Dimensions and Weight

Overall Length	5.82" (14.8 cm)
----------------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2646 SE Washington Blvd
74006-0000, OK Bartlesville
Phone: 918-876-3357
Fax: 918-876-3358

Descriptions

Description	DUAL IR/PROBE THERMOMETER
extra long description	KLEIN IR07 Dual IR/Probe Digital T
Features	The Klein Tools IR07 is a dual IR (infrared) thermometer and probe thermometer. This rugged pocket thermometer measures temperature from -40 to 572-Degrees Fahrenheit (-40 to 400-Degrees Celsius) for both IR and probe measurements. The IR thermometer has a Distance-to-Spot ratio of 8:1 and the target laser can also be used as a laser pointer. The Probe accurately measures air, liquid and surface temps and has a convenient hook for hands free indoor measurements. The IR07 quickly calculates differential tem
Long Description	The Klein Tools IR07 is a dual IR (infrared) thermometer and probe thermometer. This rugged pocket thermometer measures temperature from -40 to 572-Degrees Fahrenheit (-40 to 400-Degrees Celsius) for both IR and probe measurements. The IR thermometer has a Distance-to-Spot ratio of 8:1 and the target laser can also be used as a laser pointer. The Probe accurately measures air, liquid and surface temps and has a convenient hook for hands free indoor measurements. The IR07 quickly calculates differential tem
Product Type	Dual Ir/Probe Digital Thermometer
Special Features	Pocket Sized, IR and Probe Thermometer; Hanging Hook for Use with Air Vents

Manufacturer Information

Brand	Klein Tools
GTIN	00092644691812
Manufacturers Part Number	IR07
UPC	092644691812

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	Pocket Infrared Thermometer with Laser and Temperature Probe

Packaging

Carton	1
Package	4
Weight	3.60 oz (106.5 g)
Weight Per each	0.087

Uses, Certifications, and Standards

Application	Temperature Measurement via IR (Infrared) and Probe
standard	IEC EN 61326-1:2013; EN61326-2-3:2013