



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ISPB203 14-2/0AWG Conn *Nsi Industries*

| | |
|------------------|---|
| Catalog Number | ISPB203 |
| Manufacturer | Nsi Industries |
| Description | The Polaris ISPB2/0-3 Multi-Tap Direct Burial Single-Sided Entry Connector Features 3 Ports Sized For 2/0 - 14 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Single-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Rated For Temporary Submersion, Wet or Damp Locations and Direct Burial Applications. Installs With A Hex Key and Torque Wrench, W |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|-------------|
| Material | Aluminum |
| Number of Conductors | 3 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 2/0-14 AWG |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|--------|-----------------------|
| Color | Black |
| Finish | EPDM Rubber Insulated |

Dimensions and Weight

| | |
|------|--------------------------|
| Size | L=2.79 - W=2.65 - H=2.10 |
|------|--------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 14-2/0AWG CONN |
| extra long description | NSI ISPB2/0-3 POLARIS EDGE Connecto |
| Features | The Polaris ISPB2/0-3 3-Port Single-Sided Submersible Connector provides the simplest solution for forming a secure connection between up to three conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 2/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in hig |
| Long Description | The Polaris ISPB2/0-3 Multi-Tap Direct Burial Single-Sided Entry Connector features 3 ports sized for 2/0 - 14 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench, w |
| Product Type | Polaris Edge Connector 2/0 3 Port Epdm |
| Special Features | (3) 2/0-14 AWG - Dual Rated |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Polaris |
| GTIN | 00662381787842 |
| Manufacturers Part Number | ISPB2/0-3 |
| UPC | 662381787842 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Submersible Pedestal Connectors |

Packaging

| | |
|-----------------|-----|
| Carton | 3 |
| Weight Per each | 0.3 |

Uses, Certifications, and Standards

| | |
|--------------------------|-----------------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | ANSI C119.4, C119.1, UL486D |
| Temperature Rating | 90 C |