



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ISPBS350B 300MCM-10AWG 2PRT Polaris PDSTL Conn

*Nsi Industries*

Catalog Number	ISPBS350B
Manufacturer	Nsi Industries
Description	The Polaris ISPBS350B Multi-Tap Direct Burial Submersible In-Line Port Connector Features 2 In-Line Ports Sized For 350 MCM - 12 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Meets or Exceeds UL486D and Ansi C119.1 S
Weight per unit	0.6200 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600
Warranty	1 YEAR
Wire Size	350 MCM-12 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	EPDM Rubber Insulated

### Dimensions and Weight

Size	L=1.25 - W=8.83 - H=3.38
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	300MCM-10AWG 2PRT POLARIS PDSTL CONN
extra long description	NSI ISPBS350B POLARIS EDGE Conn 350
Features	The Polaris ISPBS350B 2-Port In-Line Entry Submersible Connector provides the simplest solution for forming a secure connection between two conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 350 MCM - 12 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric st
Long Description	The Polaris ISPBS350B Multi-Tap Direct Burial Submersible In-Line Port Connector features 2 in-line ports sized for 350 MCM - 12 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Installs with a hex key and torque wrench, without any tape or additional supplies. Meets or exceeds UL486D and ANSI C119.1 s
Product Type	Polaris Edge Conn 350 Splice Epdm Bag
Special Features	Splice 350 MCM-6 AWG - Bagged - Dual Rated

## Manufacturer Information

Brand	Nsi Industries
GTIN	00662381800657
Manufacturers Part Number	ISPBS350B
UPC	662381800657

## Taxonomies, Classifications, and Categories

Type	Submersible Pedestal Connectors
------	---------------------------------

## Packaging

Carton	1
Weight Per each	0.62

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions standard	90
Temperature Rating	ANSI C119.4, C119.1, UL486D
	90