



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

17 Lou Stroup Drive  
78801-0000, TX Uvalde  
Phone: 830-278-1938  
Fax: 830-278-1395



## J2159CRTP Hybrid Pliers - Crimper/Puller/Stripper

*Klein Tools*

Catalog Number	J2159CRTP
Manufacturer	Klein Tools
Description	Pliers Strip, Cut, Pull, Twist, Shear and Crimp With One Tool. These Hybrid Pliers Feature A Built-In Channel to Pull Steel Fish Tape Without Damaging The Wire. With Full Length, Induction Hardened Knives and A High-Leverage Design, These Hybrid Pliers Provide More Cutting Power On Hard Wire. It Easily Strips 10-14 Awg Solid and 12-16 Stranded Wire. The Wide, Knurled Head Easily Grabs and Twists Wires. Convenient Holes For Shearing 6-32 and 8-32 Bolts Plus A Crimper For Non-Insulated Connectors, Lugs and T
Weight per unit	0.6813 (lbs/each)
Product Category	Tools & Testers

### Features

Handle Length	5.01" (12.7 cm)
Jaw Length	2.04" (0 cm)
jaw thickness	0.6" (1.5 cm)
Jaw Width	1.154" (0 cm)
knife length	0.8" (2 cm)
Material	Chrome-Vanadium Steel
media	Yes
Overall Height	0.75" (2 cm)
Overall Width	2.25" (6 cm)
tether capable	No

### Material, Color, and Finish

Handle Color	Gray/Black
--------------	------------

### Dimensions and Weight

Overall Length	8.98" (22.8 cm)
----------------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

17 Lou Stroup Drive  
78801-0000, TX Uvalde  
Phone: 830-278-1938  
Fax: 830-278-1395

## Descriptions

Description	HYBRID PLIERS - CRIMPER/PULLER/STRIPPER
extra long description	KLEIN J2159CRTP Multi-Purpose Hybri
Features	Pliers strip, cut, pull, twist, shear and crimp with one tool. These hybrid pliers feature a built-in channel to pull steel fish tape without damaging the wire. With full length, induction hardened knives and a high-leverage design, these hybrid pliers provide more cutting power on hard wire. It easily strips 10-14 AWG solid and 12-16 stranded wire. The wide, knurled head easily grabs and twists wires. Convenient holes for shearing 6-32 and 8-32 bolts plus a crimper for non-insulated connectors, lugs and t
Long Description	Pliers strip, cut, pull, twist, shear and crimp with one tool. These hybrid pliers feature a built-in channel to pull steel fish tape without damaging the wire. With full length, induction hardened knives and a high-leverage design, these hybrid pliers provide more cutting power on hard wire. It easily strips 10-14 AWG solid and 12-16 stranded wire. The wide, knurled head easily grabs and twists wires. Convenient holes for shearing 6-32 and 8-32 bolts plus a crimper for non-insulated connectors, lugs and t
Product Type	Multi-Purpose Hybrid Pliers
Special Features	High-Leverage Design

## Manufacturer Information

Brand	Klein Tools
GTIN	00092644701511
Manufacturers Part Number	J2159CRTP
UPC	092644701511

## Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	High Leverage Stripping Crimping Shearing Side-Cut Hybrid Plier

## Packaging

Carton	1
Package	6
Weight	10.9 oz (308 g)
Weight Per each	0.68125

## Uses, Certifications, and Standards

Application	Strip (10-14 SLD)(12-16 STR), Bolt Shear #6-32 and #8-32, Crimps Non-Insulated Connectors, Lugs and Terminals, Cuts Screws, Nails and Most Hardened Wire
-------------	--