



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## JD 1/2-1" Direct Burial Bronze Ground Clamp

*Abb Installation Products, Inc*

|                  |   |
|------------------|---|
| Catalog Number   | JD  |
| Manufacturer     | Abb Installation Products, Inc  |
| Description      | Cast Bronze Ground Clamp For Wire Range 10 - 2, Water Pipe Size 1/2-1 Inch, Rated For Direct Burial |
| Weight per unit  | 0.1890 (lbs/each)   |
| Product Category | Ground Rods & Grounding System  |

### Features

|            |    |
|------------|----|
| insulation | No |
|------------|----|

### Material, Color, and Finish

|                    |        |
|--------------------|--------|
| Conductor Material | Bronze |
|--------------------|--------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 1/2-1" DIRECT BURIAL BRONZE GROUND CLAMP  |
| extra long description | ABB JD GRD CLAMP FOR DIR BURIAL 2 S   |
| Long Description       | Cast Bronze Ground Clamp for Wire Range 10 - 2, Water Pipe Size 1/2-1 Inch, Rated for Direct Burial |
| Product Type           | GRD Clamp For Dir Burial 2 STR-10 S   |
| Special Features       | High-strength, high conductivity copper alloy (over 80 percent copper)                              |

### Manufacturer Information

|       |                     |
|-------|---------------------|
| Brand | Blackburn Grounding |
| GTIN  | 00783786801053      |
| UPC   | 783786801053        |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods |
| Type                 | GROUND CLAMP   |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 100   |
| Weight Per each | 0.189 |

### Uses, Certifications, and Standards

|          |          |
|----------|----------|
| standard | UL E3060 |
|----------|----------|