



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



JSBT6INSWW90PIR 15W Led Disk Light W/Mot Sensor 3K/4K/5K 1050LM

Lithonia Lighting - Acuity

Catalog Number	JSBT6INSWW90PIR
Manufacturer	Lithonia Lighting - Acuity
Description	The Juno® Slimbasics™ 6IN JSBT Slim Tapered Switchable White Led Disk Light Is Designed to Be The Lowest Total Installed Cost Solution For Residential Spaces. The Matte White Aluminum Housing Is Aesthetically Pleasing Bringing A Design Element That Blends With Any Décor. The JSBT Features A Switchable White Color Temperature Switch On The Back Of The Product Allowing You to Choose Between Three (3) Easy Color Temperature Adjustments (3000K Warm White, 4000K Cool White, or 5000K Daylight), Plus It Includes
Weight per unit	0.4300 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimmable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1000 LM
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	5
Wattage	15

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	3000 ,4000 ,5000
Finish	Matte
Lens Color	Clear
Lens Material	Polycarbonate
Style	CONTEMPORARY



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

Height	1.4
Length	7.87
Width	7.72

Descriptions

Description	15W LED DISK LIGHT W/MOT SENSOR 3K/4K/5K 1050LM
extra long description	LITH JSBT 6IN SWW/2 90CRI PIR MW M6
Features	Contractor Select
Long Description	The Juno® SlimBasics™ 6in JSBT Slim Tapered Switchable White LED Disk Light is designed to be the lowest total installed cost solution for residential spaces. The matte white aluminum housing is aesthetically pleasing bringing a design element that blends with any décor. The JSBT features a switchable white color temperature switch on the back of the product allowing you to choose between three (3) easy color temperature adjustments (3000K Warm White, 4000K Cool White, or 5000K Daylight), plus it includes
Product Type	Surface Light

Manufacturer Information

Brand	JUNO
GTIN	00196182201639
Manufacturers Part Number	JSBT 6IN SWW/2 90CRI PIR MW M6
UPC	196182201639

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Surface Light

Trade Size

aperture size	6 in
---------------	------

Packaging

Carton	1
Package	6
Weight	0.43
Weight Per each	0.43

Uses, Certifications, and Standards

Application	Education,Government,Hospitality,Offices & Banks,Residential,Retail
environmental conditions	Indoor
Mounting	Flush,Surface
standard	ETLCA Title 24,ENERGY STAR,JA8