



K2C20B1 K2C20B1 Burndy LLC

Catalog Number	K2C20B1
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, 2 Cables to Flat, 10 - 5 Awg (STR) / 10 - 4 Awg (Sol), 5/16" Stud.
Weight per unit	0.0800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Bronze Alloy, Leaded
pallet quantity	19800

Descriptions

Description	K2C20B1
extra long description	BUR K2C20B1 10-5 STR 27/32 POST 2 C
Long Description	Mechanical Grounding Connector, 2 Cables to Flat, 10 - 5 AWG (Str) / 10 - 4 AWG (Sol), 5/16" Stud.
Product Type	Mechanical
Special Features	Features: SERVIT POST Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar, One-Wrench Installation, Conductor Type: Run: Commercial Stranded Copper, Commercial Solid Copper, Cross Flats: 11/16, 1/2 IN, Height: 2-1/8 IN, Stud Size: 5/16-18, Dimension B: 27/32 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810257050
Manufacturers Part Number	K2C20B1
UPC	781810257050

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	KC and K2C Series

Packaging

Carton	1
Weight Per each	0.08

Uses, Certifications, and Standards

Application	For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial
standard	UL467