



K2C22B1 3STR Split Bolt Conn Burndy LLC

| | |
|------------------|--|
| Catalog Number | K2C22B1 |
| Manufacturer | Burndy LLC |
| Description | Mechanical Grounding Connector, 2 Cables to Flat, 10 - 3 Awg (STR) / 10 - 2 Awg (Sol). |
| Weight per unit | 0.1300 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|----------------------|
| Material | Bronze Alloy, Leaded |
| pallet quantity | 14850 |

Descriptions

| | |
|------------------------|---|
| Description | 3STR SPLIT BOLT CONN |
| extra long description | BUR K2C22B1 10-3 STR 31/32 POST 2 C |
| Long Description | Mechanical Grounding Connector, 2 Cables to Flat, 10 - 3 AWG (Str) / 10 - 2 AWG (Sol). |
| Product Type | Mechanical |
| Special Features | Features: SERVIT POST Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar, One-Wrench Installation, Conductor Type: Run: Commercial Stranded Copper, Commercial Solid Copper, Cross Flats: 3/4, 5/8 IN, Height: 2-3/8 IN, Dimension B: 31/32 IN, Stud Size: 3/8-16 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | BURNDY |
| GTIN | 00781810257159 |
| Manufacturers Part Number | K2C22B1 |
| UPC | 781810257159 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------|
| Category Description | SPLIT BOLTS |
| Type | KC and K2C Series |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.13 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial |
| standard | UL467 |