



## K2C28B1 4/0 Split Bolt Conn

Burndy LLC

Catalog Number	K2C28B1
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Flat, 1-4/0 Awg, 5/8" Stud.
Weight per unit	0.5200 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	COPPER ALLOY
----------	--------------

### Descriptions

Description	4/0 SPLIT BOLT CONN
extra long description	BUR K2C28B1 1-4/0 STR 1 1/4 POST 2
Long Description	Mechanical Grounding Connector, Cable to Flat, 1-4/0 AWG, 5/8" Stud.
Product Type	1-4/0 STR 1 1/4 Post 2 C
Special Features	Features: SERVIT POST Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar, One-Wrench Installation, Conductor Type: Run: Commercial Stranded Copper, Commercial Solid Copper, Cross Flats: 1-1/2, 1-3/16 IN, Height: 3-3/4 IN, Dimension B: 1-1/4 IN, Stud Size: 5/8-11

### Manufacturer Information

Brand	BURNDY
GTIN	00781810257555
Manufacturers Part Number	K2C28B1
UPC	781810257555

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KC and K2C Series

### Packaging

Carton	1
Weight Per each	0.52

### Uses, Certifications, and Standards

Application	For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial
standard	UL467