



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## K4141C 3000W 120V Photo Cell

*Intermatic Inc.*

Catalog Number	K4141C
Manufacturer	Intermatic Inc.
Description	Stem Mount Thermal Photocontrol, 120 V, 25 A
Weight per unit	0.2420 (lbs/each)
Product Category	Lighting Photocells

### Features

connection	Color Coded Lead
Connection Type	1/2 IN - 14 NPT Thread
supply voltage	120

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	1-9/16 LENGTH X 1-9/16 WIDTH X 3 DEPTH IN, 4 LENGTH X 4 WIDTH X 7.6 DEPTH CM
------	--

### Descriptions

Description	3000W 120V PHOTO CELL
extra long description	INT-MAT K4141C Stem Mount Thermal P
Features	These photocontrols install on standard outdoor light fixtures and electrical boxes with 1 2"-14 NPSM thread or 7 8" knock-out holes for dusk-to-dawn ON/OFF control of outdoor lighting.
Long Description	Stem Mount Thermal Photocontrol, 120 V, 25 A
Product Type	Stem Mount Thermal Photocontrol, 120 V, 25 A
Special Features	Features: Cadmium Sulfide Photocell, Sonic-Welded Polycarbonate Housing, 6 IN Wire Leads, Light Level Slide Adjustment

### Manufacturer Information

Brand	Intermatic Inc.
GTIN	00078275029583
Manufacturers Part Number	K4141C
UPC	078275029583

### Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells
Type	Thermal Type Photo Cell

### Packaging

Carton	1
Package	12
Weight Per each	0.242



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Dusk to Dawn Lighting Control
Frequency Rating	50/60
Mounting	Stem Mount
Operating Temperature	-40 to +158 DEG F -40 to +70 DEG C
standard	CSA, Title CA 20 Listed, California Title 24 Compliant