

**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

KA29U  
 7818103701555  
 6STR-250 DUAL RATED  
 Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Width (in)	1.00
Length (in)	2.00
Bolt Hole Size (in)	0.31
Thickness	0.25
D - in	0.94
Pad Width (in)	1.02
N (in)	0.47
General	
Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 6 AWG (Str)-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	6 STR- 250 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	6-250
Physical	
Installation Torque	275
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	5/16
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109


Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

KA29U  
 7818103701555  
 6STR-250 DUAL RATED  
 Active

**Web Use**  
 BURNDY Product Line



Dimensional	
Width (in)	1.00
Length (in)	2.00
Bolt Hole Size (in)	0.31
Thickness	0.25
D - in	0.94
Pad Width (in)	1.02
N (in)	0.47
General	
Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 6 AWG (Str)-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	6 STR- 250 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	6-250
Physical	
Installation Torque	275
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	5/16
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175