



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KS34 Servit 2/0 STR - 500 Burndy LLC

Catalog Number	KS34
Manufacturer	Burndy LLC
Description	Copper Split Bolt, Cu: 2/0 Awg (STR)-500 Kcmil (Run & Tap).
Weight per unit	0.8080 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
----------	--------

Descriptions

Description	SERVIT 2/0 STR - 500
extra long description	BUR KS34 SERVIT 2/0 STR - 500
Long Description	Copper Split Bolt, Cu: 2/0 AWG (Str)-500 kcmil (Run & Tap).
Product Type	Mechanical
Special Features	Features: Compact, High Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Season Cracking And Corrosion, The SERVIT Provides Maximum Pressure And Assures A Secure Connection On All Combinations Of Run And Tap Conductors, Installation Torque: 825 IN-LB, Conductor Type: Run: Commercial Stranded And Solid Copper, Stranded Copperweld, Tap: Commercial Stranded And Solid Copper, Stranded Copperweld, Width: 1.48 IN, Length: 2.79 IN, Cross Fla

Manufacturer Information

Brand	BURNDY
GTIN	00781810014509
Manufacturers Part Number	KS34
UPC	781810014509

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	KS

Packaging

Carton	1
Package	12
Weight Per each	0.808

Uses, Certifications, and Standards

Application	For Direct Burial Cables
-------------	--------------------------