



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTLF32T8841HP 32W T8 48" 41K 3100LM 85CRI Med Bi-Pin Base

Keystone Technologies

Catalog Number	KTLF32T8841HP
Manufacturer	Keystone Technologies
Description	F32T8, 4100K, 85 Cri, High Performance Lamps, 25 PCS Per Carton
Weight per unit	0.3800 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Ballast Type	N/A
beam angle	360 Deg
Circuit Type	N/A
Input Voltage	Ballast Dependent
ip rating	N/A
lumens	3100
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	32
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4100
housing color	N/A

Descriptions

Construction	Frosted Glass
Description	32W T8 48" 41K 3100LM 85CRI MED BI-PIN BASE
extra long description	Key KTL-F32T8-841-HP-DP Ignitor for
Long Description	F32T8, 4100K, 85 CRI, HIGH PERFORMANCE LAMPS, 25 PCS PER CARTON
Product Type	Ignitor For 750W Pulse Start MH

Manufacturer Information

Brand	Keystone
GTIN	00890949006412
Manufacturers Part Number	KTL-F32T8-841-HP-DP
UPC	890949006412



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Packaging

Carton 25

Weight Per each 0.38

Uses, Certifications, and Standards

Energy Star N