



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L11.5T848GC840S 11.5W Led T8 48" 40K Ballast Compatible

*Keystone Technologies*

Catalog Number	L11.5T848GC840S
Manufacturer	Keystone Technologies
Description	11.5W Led T8 Tube, Shatter-Proof Coated Glass, Ballast Compatible, 4 FT., 4000K, Smartdrive
Weight per unit	0.6500 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	Ballast Dependent
ip rating	N/A
lumens	1800
Nominal Length	36 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	11.5
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

### Descriptions

Construction	N/A
Description	11.5W LED T8 48" 40K BALLAST COMPATIBLE
extra long description	Key KT-LED11.5T8-48GC-840-S-CP 11.5
Long Description	11.5W LED T8 TUBE, SHATTER-PROOF COATED GLASS, BALLAST COMPATIBLE, 4 FT., 4000K, SMARTDRIVE
Product Type	11.5 W, 1800 Lumen, 4', 220' Beam Angle, Ballast Compatible,

### Manufacturer Information

Brand	Keystone
GTIN	00890949012925
Manufacturers Part Number	KT-LED11.5T8-48GC-840-S-CP
UPC	890949012925



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
--------	----

Weight Per each	0.65
-----------------	------

## Uses, Certifications, and Standards

Energy Star	Y
-------------	---