

Locking devices

Complex environment locking devices

Product description

3-pole, 4-wire grounding
30A, 125/250V/AC
NEMA L14-30




L14-30R L14-30P




CRL1430P



CRL1430C



CRL1430R



L1430RW

Dimensional information:
D-34-35

Specification information:
Watertight industrial plugs & connectors: D-38
Watertight industrial receptacles: D-39
Severe duty industrial plugs & connectors: D-40
Corrosion resistant: D-41

Plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
30	125/250	L14-30	Watertight	0.43-1.15" (10.9-29.2mm)	Y	□ L1430PW	□ L1430CW	•	•
			Watertight	0.43-1.15" (10.9-29.2mm)	BK	□ L1430PWBK	□ L1430CWBK	•	•
			Severe duty	0.63-1.16" (15.9-29.4mm)	Y & BK	□ L1430PY	□ L1430CY	•	•
			Safety grip corrosion resistant	0.63-1.16" (15.9-29.4mm)	Y	□ CRL1430P	□ CRL1430C	•	•

Receptacles




Rating A	V/AC	NEMA	Description	Color	Single receptacle catalog no.		
30	125/250	L14-30	Watertight	Y	□ L1430RW	•	•
			Watertight	BK	□ L1430RWBK	•	•
			Corrosion resistant	Y	□ CRL1430R*	•	•

* Only UL Listed, CSA certified and Fed Spec certified

Complex environment locking devices

Product description

3-pole, 4-wire grounding
30A, 3Ø 250V/AC
NEMA L15-30



L15-30R L15-30P

3Ø plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
30	250	L15-30	3Ø watertight	0.43-1.15" (10.9-29.2mm)	Y	□ L1530PW	□ L1530CW	•	•
			3Ø watertight	0.43-1.15" (10.9-29.2mm)	BK	□ L1530PWBK	□ L1530CWBK	•	•
			3Ø severe duty	0.63-1.16" (15.9-29.4mm)	Y & BK	□ L1530PY	□ L1530CY	•	•
			3Ø safety grip corrosion resistant	0.63-1.16" (15.9-29.4mm)	Y	□ CRL1530P	□ CRL1530C	•	•

3Ø receptacles



Rating A	V/AC	NEMA	Description	Color	Single receptacle catalog no.		
30	250	L15-30	3Ø watertight	Y	□ L1530RW	•	•
			3Ø watertight	BK	□ L1530RWBK	•	•

Color information:

BK (Black), Y (Yellow)



Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32