

30 Amp NEMA L1430 Single Receptacle

L1430R



Turnlok Single Receptacle 4wire 30amp
125/250v



features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

specifications

General Info

Type: Single, Receptacles
Number Of Wires: 4

Listing Agencies/Third Party Information

CSA Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: 498
UL Standard: Yes

UN SPS C: 39121403

Dimensions

Depth U S: 1.28"

Height U S: 3.28"

Width U S: 1.61"

Technical Information

Amps: 30 Amp

NEMA Configuration Number: L1430

Volts: 125/250V

Volts A C: 125/250

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant