

# Specifications



## Eaton L1520PW

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 20A, Industrial, 250V, Back wiring, Yellow, Steel, Watertight, L15-20, Three-pole, Four-wire, Santoprene, 0.36 to 0.84 in, IP67

### General specifications

|                             |                                                   |
|-----------------------------|---------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Arrow Hart watertight locking plug          |
| <b>CATALOG NUMBER</b>       | L1520PW                                           |
| <b>UPC</b>                  | 040893642048                                      |
| <b>PRODUCT LENGTH/DEPTH</b> | 6 in                                              |
| <b>PRODUCT HEIGHT</b>       | 3.5 in                                            |
| <b>PRODUCT WIDTH</b>        | 4 in                                              |
| <b>PRODUCT WEIGHT</b>       | 1.025 lb                                          |
| <b>COMPLIANCES</b>          | RoHS Compliant                                    |
| <b>CERTIFICATIONS</b>       | UL Listed<br>NOM<br>CSA certified<br>cULus Listed |
| <b>PRODUCT TYPE</b>         | Watertight                                        |

## Electrical Ratings

|                      |                |
|----------------------|----------------|
| AMPERAGE RATING      | 20A            |
| DEGREE OF PROTECTION | IP67           |
| NEMA CONFIGURATION   | L15-20         |
| NUMBER OF POLES      | Three-pole     |
| NUMBER OF WIRES      | 4<br>Grounding |
| TORQUE RATING        | 14-16 lbf-inch |
| VOLTAGE RATING       | 3Ø 250 V       |

## Installation Specifications

|                     |            |
|---------------------|------------|
| ALLOWABLE WIRE SIZE | #18-10 AWG |
| WIRING METHOD       | Back       |

## Product Specifications

|                    |                                                 |
|--------------------|-------------------------------------------------|
| APPLICATION        | Industrial                                      |
| CORD DIAMETER      | 0.36-0.84 in                                    |
| DESIGN TYPE        | Watertight locking plug                         |
| DEVICE GRADE       | Extra heavy-duty industrial specification grade |
| FACE/BODY MATERIAL | Nylon                                           |
| MATERIAL           | Santoprene                                      |
| SPECIAL FEATURES   | Watertight                                      |
| TYPE               | Locking plug                                    |

## Environmental Specifications

|                             |         |
|-----------------------------|---------|
| ENVIRONMENTAL<br>RESISTANCE | NEMA 6  |
|                             | IP67    |
|                             | NEMA 6P |
|                             | NEMA 4  |
|                             | NEMA 4X |

## Material Specifications

|                  |                     |
|------------------|---------------------|
| COLOR            | Yellow              |
| CONTACT MATERIAL | Nickel plated brass |

## Resources

|                                  |                                                                                            |
|----------------------------------|--------------------------------------------------------------------------------------------|
| SPECIFICATIONS AND<br>DATASHEETS | <a href="#">Eaton Specification Sheet - L1520PW</a>                                        |
|                                  | <a href="#">Arrow Hart watertight locking plugs, connectors and receptacles spec sheet</a> |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

