

Specifications

Eaton L1630PW



Eaton Arrow Hart watertight locking plug, #18-10 AWG, 30A, Industrial, 480V, Back, Yellow, Steel, Watertight, L16-30, Three-pole, Four-wire, Santoprene, 0.43 to 1.15 in, IP67



General specifications

PRODUCT NAME	Eaton Arrow Hart watertight locking plug
CATALOG NUMBER	L1630PW
UPC	040893642123
PRODUCT LENGTH/DEPTH	6.75 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	0.81 lb
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Watertight locking plug

Electrical Ratings

AMPERAGE RATING	30A
NEMA CONFIGURATION	L16-30
NUMBER OF POLES	Three-pole
NUMBER OF WIRES	4
TORQUE RATING	20 lbf-inch
VOLTAGE RATING	480 V

Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.43-1.15 in
MATERIAL	Santoprene
SPECIAL FEATURES	Watertight locking plug

Environmental Specifications

ENVIRONMENTAL RESISTANCE	Watertight
--------------------------	------------

Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Steel

Resources

[Eaton Specification Sheet - L1630PW](#)

SPECIFICATIONS AND DATASHEETS

[Arrow Hart watertight locking plugs, connectors and receptacles spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

