



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

700 Industry Way Suite 10
75078-0000, TX Prosper
Phone: 469-899-3981
Fax: 469-899-3982



L20N 2/0 2-Hole Long Barrel Compression Lug 1/2" Bolt

Nsi Industries

Catalog Number	L20N
Manufacturer	Nsi Industries
Description	2 Hole Long Barrel Copper Compression Lug 2/0 Awg - 1/2" Bolt Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. Allows Easy Inspection Of The Termination to Assure Complete Cable Insertion. Tin-Plated to Provide Corrosion and Low Contact Resistance. Marked With Die Index and Color Coded. Listed For 35KV Maximum When Properly Installed. Rated 600V. Culus 486A/B Listed. UL467 Listed On Sizes 6 Awg - 3/0 Awg. Temperature Rating 90 Degrees C.
Weight per unit	0.1500 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	2/0 AWG (STR)
Material	Copper
Number of Holes	2
Stud Size	1/2
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
Finish	Tin Plated

Dimensions and Weight

Size	L=4.61 - W=.810 - OD=.560 - ID=.440
------	-------------------------------------



Descriptions

Description	2/0 2-HOLE LONG BARREL COMPRESSION LUG 1/2" BOLT
extra long description	NSI L20N CU CMP Lug Long 2/0 AWG Ne
Features	2 Hole Long Barrel Copper Compression Lug 2/0 AWG - 1/2" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C.
Long Description	2 Hole Long Barrel Copper Compression Lug 2/0 AWG - 1/2" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C.
Product Type	Cu CMP Lug Long 2/0 Awg Nema MTG Spac
Special Features	2/0 AWG (STR) - 1/2 Mounting Holes - 1 3/4 Hole Spacing

Manufacturer Information

Brand	NSI
GTIN	00662381035103
Manufacturers Part Number	L20N
UPC	662381035103

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - Two Hole

Packaging

Carton	1
Package	25
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/2 Mounting Holes
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)