

Specifications



Eaton L520PW

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 20A, Industrial, 125V, Back wiring, Yellow, Steel, Watertight, L5-20, Two-pole, Three-wire, Santoprene, 0.36 to 0.84 in, IP67

General specifications

PRODUCT NAME	Eaton Arrow Hart watertight locking plug
CATALOG NUMBER	L520PW
UPC	040893641744
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	1.025 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Watertight

Electrical Ratings

AMPERAGE RATING	20A
NEMA CONFIGURATION	L5-20
NUMBER OF POLES	Two-pole
NUMBER OF WIRES	Grounding 3
TORQUE RATING	14-16 lbf-inch
VOLTAGE RATING	125 V

Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.36-0.84 in
DESIGN TYPE	Watertight locking plug
DEVICE GRADE	Extra heavy-duty industrial specification grade
FACE/BODY MATERIAL	Nylon
MATERIAL	Santoprene
SPECIAL FEATURES	Watertight
TYPE	Locking plug

Environmental Specifications

ENVIRONMENTAL RESISTANCE	NEMA 6P
	NEMA 4
	NEMA 6
	IP67
	NEMA 4X

Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Nickel plated brass

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - L520PW
	Arrow Hart watertight locking plugs, connectors and receptacles spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

