



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L810 #8AWG #10BLT 1H LNG BRL Cu CMP Lug

Nsi Industries

Catalog Number	L810
Manufacturer	Nsi Industries
Description	1 Hole Long Barrel Copper Compression Lug 8 Awg - 10 Bolt Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Low Contact Resistance. Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed and to Cable Manufacturer Instructions. Temperature Rating 90 Degrees C. .
Weight per unit	2.2 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Cable Size	# 8 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	#10
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Red
Finish	Tin Plated

Dimensions and Weight

Size	L=1.52 - W=.420 - OD=.295 - ID=.205
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	#8AWG #10BLT 1H LNG BRL CU CMP LUG
extra long description	NSI L810 #8 Awg Max Wire Size, #10
Features	1 Hole Long Barrel Copper Compression Lug 8 AWG - 10 Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Long Description	1 Hole Long Barrel Copper Compression Lug 8 AWG - 10 Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Product Type	#8 Awg Max Wire Size, #10 Stud Size, Tin-Plated Long Barrel
Special Features	# 8 AWG (STR) - # 10 Mounting Hole

Manufacturer Information

Brand	Nsi Industries
GTIN	00662381336255
Manufacturers Part Number	L810
UPC	662381336255

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - One Hole

Packaging

Carton	1
Weight Per each	2.2

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	# 10 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)