



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LB250DCG 2-1/2" LB FM5 Cond BC&G *Appleton/Oz Gedney*

Catalog Number	LB250DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Aluminum Threaded For Rigid Conduit and Imc, Type LB, Set Screw, Material: Conduit Body: Diecast, Copperfree Aluminum/Epoxy Powder Coat, Cover: Stamped Aluminum, Natural Finish, Gasket: Neoprene, UI Standard: 514A, Trade Size: 2-12
Weight per unit	4.0 (lbs/each)
Product Category	Alum

Material, Color, and Finish

Finish	Epoxy Powder Coat;Other
--------	-------------------------

Dimensions and Weight

Height	6.03
Hub Size	3
Length	13.14
Width	4.33

Descriptions

Description	2-1/2" LB FM5 COND BC&G
extra long description	EGS LB250DCG 2-1/2 THD ALUM LB BDY
Long Description	EMT Conduit Bodies, Aluminum Threaded for rigid conduit and IMC, Type LB, Set Screw, Material: Conduit body: diecast, copperfree aluminum/epoxy powder coat, Cover: stamped aluminum, natural finish, Gasket: neoprene, UL Standard: 514A, Trade Size: 2-12
Product Type	2-1/2 THD Alum LB Bdy CVR GSKT
Special Features	2-1/2 IN Trade Size, Type LB Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #4/0 AWG, Volume 153.00 IN ³ , For Use With Rigid and IMC Conduit, Furnished With Cover and Gasket

Manufacturer Information

Brand	Appleton
GTIN	00687855001293
Manufacturers Part Number	LB250DCG
UPC	687855001293

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4

Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A