

Eaton LBY35 SA

Catalog Number: LBY35 SA

Eaton Crouse-Hinds series Condulet LBY elbow, Rigid/IMC, Copper-free aluminum, 90°, 1"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet LBY elbow	LBY35 SA
	UPC
	782274277073
Product Length/Depth	Product Height
2.5 in	3.25 in
Product Width	Product Weight
2.5 in	1 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

Product specifications

Conduit type

Rigid/IMC

Material

Copper-free aluminum

Shape

90° angle

Trade size

1"

Resources

Catalogs

[Crouse-Hinds series Condulet LBH, LBY and ET Bodies, Elbows and Tees catalog page](#)

Certification reports

[Explosionproof Conduit Unions, Elbows and Tees Canadian certification](#)

[Pull Elbows and Tees - Rigid-IMC UL certification \(LBY and ET\)](#)

[Explosionproof Conduit Unions, Elbows and Tees UL certification](#)

[Pull Elbows and Tees - Rigid-IMC Canadian certification \(LBY and ET\)](#)

Specifications and datasheets

[Eaton Specification Sheet - LBY35 SA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)