



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LC200DCG 2" Cond Body C/G *Appleton/Oz Gedney*

Catalog Number	LC200DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Aluminum Threaded For Rigid Conduit and Imc, Material: Conduit Body: Diecast, Copperfree Aluminum/Epoxy Powder Coat, Cover: Stamped Aluminum, Natural Fi Nish, Gasket: Neoprene, UI Standard: 514A, Trade Size: 2", Lengt
Weight per unit	3.0 (lbs/each)
Product Category	Alum

Material, Color, and Finish

Finish	Epoxy Powder Coat;Other
--------	-------------------------

Dimensions and Weight

Height	3.65
Hub Size	2
Length	10.71
Width	3.1

Descriptions

Description	2" COND BODY C/G
extra long description	EGS LC200DCG 2 IN THD ALUM LC BDY C
Long Description	EMT Conduit Bodies, Aluminum Threaded for Rigid Conduit and IMC, Material: Conduit body: diecast, copperfree aluminum/epoxy powder coat, Cover: stamped aluminum, natural fi nish, Gasket: neoprene, UL Standard: 514A, Trade Size: 2", Lengt
Product Type	2 In THD Alum LC Bdy CVR GSKT
Special Features	2 IN Trade Size, Type LC Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #4/OAWG, Volume 69.50 IN ³ , For Use With Rigid and IMC Conduit, Furnished With Stamped Aluminum Cover and Neoprene Gasket

Manufacturer Information

Brand	Appleton
GTIN	00687855000647
Manufacturers Part Number	LC200DCG
UPC	687855000647

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	3

Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A