



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCCX438DL #4 2HOLE 3/8SP Panduit Corporation

| | |
|------------------|--|
| Catalog Number | LCCX438DL |
| Manufacturer | Panduit Corporation |
| Description | Two-Hole, Flex Lug, Long Barrel, #4 Awg Wire, 3/8 Stud Hole, 1 Hole Spacing. |
| Weight per unit | 2.2 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|-------------------|
| Material | Tin-Plated Copper |
| media | Yes |
| Number of Holes | 2 |
| Stud Size | 3/8 |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Dimensions and Weight

| | |
|------|---|
| Size | #4 AWG Class B, C, G, H, I, K, M and #5, #4, #3 AWG DLO |
|------|---|

Descriptions

| | |
|------------------------|---|
| Description | #4 2HOLE 3/8SP |
| extra long description | PAN LCCX4-38D-L Pan-Lug™ LCCX4-38D- |
| Long Description | Two-hole, flex lug, long barrel, #4 AWG wire, 3/8 stud hole, 1 hole spacing. |
| Product Type | Pan-Lug™ LCCX4-38D-L Compression Connectors - Lugs |
| Special Features | Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 V |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983425501 |
| Manufacturers Part Number | LCCX4-38D-L |
| UPC | 074983425501 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Compression Lug |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 2.2 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|----------|--|
| Mounting | 1-1/8 |
| standard | CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File #E52164, ABS approved |