



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED12A19DIM0840U 12W Led A19 40K Dim 1100LM *Sylvania-Ledvance*

Catalog Number	LED12A19DIM0840U
Manufacturer	Sylvania-Ledvance
Description	Led A19, 12W, Dimmable, 80CRI, 1100 Lumen, 4000K, 15000 Life, E26 Medium Base, Frosted Finish
Weight per unit	0.3270 (lbs/each)
Product Category	Lighting

### Features

average life	15000
Base	E26 Medium
Lamp Type	LED A19
lumens	1,100
Shape	A19
Voltage	120.00 V
Voltage Rating	120.00
Wattage	12.00

### Material, Color, and Finish

color rendering index (cri)	80
Style	A-shape

### Dimensions and Weight

Size	2.36
------	------

### Descriptions

Description	12W LED A19 40K DIM 1100LM
extra long description	SYL LED12A19DIM0840URP/41191 LED12A
Long Description	LED A19, 12W, Dimmable, 80CRI, 1100 Lumen, 4000K, 15000 Life, E26 Medium Base, FROSTED Finish
Product Type	LED12A19DIM0840URP 6/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135411915
Manufacturers Part Number	LED12A19DIM0840URP/41191
UPC	046135411915

### Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
----------------------	------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	6
Weight Per each	0.327

## Uses, Certifications, and Standards

standard	RoHS
----------	------