




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED13T860P1S865D 5' 13W Led Signhero 65K 180DEG Ballast Bypass *Keystone Technologies*

Catalog Number	LED13T860P1S865D
Manufacturer	Keystone Technologies
Description	60IN Led Sign Tube, 6500K, Single Sided Output and Rotatable R17D End Caps, 13W, 120-277V Input
Weight per unit	1.3 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	180 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1625
Nominal Length	60 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	13
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	6500
housing color	N/A

Descriptions

Construction	N/A
Description	5' 13W LED SIGNHERO 65K 180DEG BALLAST BYPASS
extra long description	Key KT-LED13T8-60P1S-865-D /G2 60"
Long Description	60IN LED SIGN TUBE, 6500K, SINGLE SIDED OUTPUT AND ROTATABLE R17D END CAPS, 13W, 120-277V INPUT
Product Type	60", 13W, 1, 625 Lumens, 180' Beam Spread, Single Sided Lamps

Manufacturer Information

Brand	Keystone
GTIN	00843654132723
Manufacturers Part Number	KT-LED13T8-60P1S-865-D /G2
UPC	843654132723



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 9

Weight Per each 1.28

Uses, Certifications, and Standards

Energy Star N