



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED14A19F85010YV 14W Led A19 50K 80CRI 1500LM ND *Sylvania-Ledvance*

Catalog Number	LED14A19F85010YV
Manufacturer	Sylvania-Ledvance
Description	Led A19, 14W 80CRI, 1500 Lumen, 5000K, 11000 Life, E26 Medium Base, Frosted Finish
Weight per unit	0.3100 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

Base	E26 Medium
Lamp Type	LED A19
lumens	1,500
Shape	A19
Voltage	120.00 V
Voltage Rating	120.00
Wattage	14.00

Material, Color, and Finish

color rendering index (cri)	80
Style	A-shape

Dimensions and Weight

Size	2.36
------	------

Descriptions

Description	14W LED A19 50K 80CRI 1500LM ND
extra long description	SYL LED14A19F85010YVRP/79294 LED14A
Long Description	LED A19, 14W 80CRI, 1500 Lumen, 5000K, 11000 Life, E26 Medium Base, FROSTED Finish

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135792946
Manufacturers Part Number	79294
UPC	046135792946

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
----------------------	------------------------

Packaging

Carton	1
Package	6
Weight Per each	0.31

Uses, Certifications, and Standards

standard	cETLus
----------	--------