



LED Dimmable Recessed Retrofits

TCP's Dimmable Retrofit Kits are the perfect choice for new construction and retrofit opportunities when a sleek, integrated look is preferred.

Limitless options for the following applications:

- Dimmable 6", 5" & 4" downlight applications

Great features and benefits:

- 120W, 85W, 75W, 65W and 50W BR40/BR30/R20 downlight replacement options
- Excellent color consistency (CRI)
- Smooth, uniform dimming from 100% - 0.5%
- Highly efficient LEDs and Driver
- Long Life: 35,000 hours
- Available in 2700K, 3000K, 4100K and 5000K
- Easy installation — pigtail and spring clips



4" Dimmable HiCRI Recessed Retrofit



5/6" Dimmable HiCRI Recessed Retrofit

90 CRI
50 R9



4" Dimmable Recessed Retrofit



5/6" Dimmable Recessed Retrofit



LED
we know light.™





LED Dimmable Recessed Retrofits Specifications

LED	35,000 hours average rated life, 120 volts
------------	--------------------------------------------

Applications:

Ideal for dimmable 6", 5" & 4" downlight applications



Perfect for retrofit or new construction recessed downlight applications

Features and Benefits

- 5/6" unit ideal for replacing dimmable 65W, 85W and 120W incandescent alternatives in 5" and 6" recessed cans
- 4" unit ideal for replacing 50W and 75W incandescent alternatives in a 4" recessed can
- Excellent Color Consistency and CRI
- Smooth, uniform dimming
- Highly efficient LEDs and Driver
- Long Life: 35,000 hours
- UL approved for damp locations
- Easy installation and integrated trim
- Shatter Resistant



LDRACCGU24 - GU24 Adapter

Catalog Number	
Notes	Type



Specifications

	14W	11W	10W	9W
Recessed Downlight Size:	5", 6"	5", 6"	4"	4"
Input Line Voltage:	120 VAC	120 VAC	120 VAC	120 VAC
Input Power	14 W	11 W	10 W	9 W
Input Line Frequency	50/60HZ	50/60HZ	50/60HZ	50/60HZ
Lamp Life (Rated)	35,000 hrs	35,000 hrs	35,000 hrs	35,000 hrs
Minimum Starting Temp	-30°C	-30°C	-30°C	-30°C

IC-rated for direct contact with insulation



- LED11DR5627K
- LED11DR5630K
- LED11DR5641K
- LED11DR5650K
- LED14DR5627K
- LED14DR5630K
- LED14DR5641K
- LED14DR5650K



- LED10DR427K
- LED10DR430K
- LED10DR435K
- LED10DR441K
- LED10DR450K



- L11DR56D3527K95
- L11DR56D3530K95



- L9DR4D3527K95
- L9DR4D3530K95



5 YEAR WARRANTY*

*Based on 12 hours use per day

For the most up-to-date specs, please visit www.tcpi.com

TCP®

325 Campus Dr. | Aurora, Ohio 44202 | P: 800-324-1496 | tcpi.com

©TCP AUG 2017/WF72602 ALL





LED Dimmable Recessed Retrofits Specifications

Smooth Uniform Dimming

5/6" Recessed Retrofits

Item #	ENERGY STAR rated	Description	Life Hours	Replacement	Voltage	Wattage	Lumens	LPW	CCT	CRI	Case Qty
Downlight Retrofits compatible with 5/6" recessed cans											
LED14DR5627K	★	LED 14W 5/6" Recessed Downlight - 2700K	35,000	120	120	14	1250	89.3	2700K	80	6
LED14DR5630K	★	LED 14W 5/6" Recessed Downlight - 3000K	35,000	120	120	14	1300	92.9	3000K	80	6
LED14DR5641K	★	LED 14W 5/6" Recessed Downlight - 4100K	35,000	120	120	14	1300	92.9	4100K	80	6
LED14DR5650K	★	LED 14W 5/6" Recessed Downlight - 5000K	35,000	120	120	14	1350	96.4	5000K	80	6
LED11DR5627K	★	LED 11W 5/6" Recessed Downlight - 2700K	35,000	85	120	11	800	72.7	2700K	80	6
LED11DR5630K	★	LED 11W 5/6" Recessed Downlight - 3000K	35,000	85	120	11	850	77.3	3000K	80	6
LED11DR5641K	★	LED 11W 5/6" Recessed Downlight - 4100K	35,000	85	120	11	900	81.8	4100K	80	6
LED11DR5650K	★	LED 11W 5/6" Recessed Downlight - 5000K	35,000	85	120	11	950	86.4	5000K	80	6
Hi CRI Downlight Retrofits compatible with 5/6" recessed cans											
L11DR56D3527K95**	★	LED 11W 5/6" Recessed Downlight - 2700K	35,000	65	120	11	700	63.6	2700K	90	6
L11DR56D3530K95**	★	LED 11W 5/6" Recessed Downlight - 3000K	35,000	65	120	11	750	68.2	3000K	90	6

4" Recessed Retrofits

Downlight Retrofits compatible with 4" recessed cans											
LED10DR427K	★	LED 10W 4" Recessed Downlight - 2700K	35,000	75	120	10	750	75.0	2700K	80	6
LED10DR430K	★	LED 10W 4" Recessed Downlight - 3000K	35,000	75	120	10	750	75.0	3000K	80	6
LED10DR435K		LED 10W 4" Recessed Downlight - 3500K	35,000	75	120	10	620	62.0	3500K	80	6
LED10DR441K	★	LED 10W 4" Recessed Downlight - 4100K	35,000	75	120	10	800	80.0	4100K	80	6
LED10DR450K	★	LED 10W 4" Recessed Downlight - 5000K	35,000	75	120	10	800	80.0	5000K	80	6
Hi CRI Downlight Retrofits compatible with 4" recessed cans											
L9DR4D3527K95**	★	LED 9W 4" Recessed Downlight - 2700K	35,000	50	120	9	550	61.1	2700K	90	6
L9DR4D3530K95**	★	LED 9W 4" Recessed Downlight - 3000K	35,000	50	120	9	550	61.1	3000K	90	6

Accessory

LDRACCGU24 GU24 Adapter

*JAB Compliant

+All Plastic Body



5 YEAR WARRANTY*

*Based on 12 hours use per day

For the most up-to-date specs, please visit www.tcpi.com

TCP®

325 Campus Dr. | Aurora, Ohio 44202 | P: 800-324-1496 | tcpi.com

©TCP AUG 2017/WF72602.ALL



CREATING BEAUTY

TCP has a **20-year history in energy-efficient lighting.**

Thanks to our **cutting edge technology** and manufacturing

expertise, we have shipped billions of high quality lamps and our

integrated technology and manufacturing

provides **expedited time-to-market.** With TCP, you can

count on unique lighting products designed to meet very specific needs—

lighting that transforms your surroundings and envelopes you in warmth—

lighting that generates beauty with every flip of the switch.

LED

For more information on the quality and care TCP can deliver, call us at **800.324.1496** or visit tcp.com

325 Campus Dr. | Aurora, Ohio 44202 | P: 800-324-1496 | F: 877-487-0516