



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120
75041-0000, TX Garland
Phone: 214-503-7227
Fax: 214-503-9766



LED15T848GC835X 15W Led T8 48" 35K Combo *Keystone Technologies*

Catalog Number	LED15T848GC835X
Manufacturer	Keystone Technologies
Description	Linear Fluorescent Led Lamp, Linear, Single Ended, Instant Start Type; 47.5 Inch; UI (Canada and Us), UI, NSF/Ansi, DLC Approval; Food Equipment, Splash Zone, Dry and Damp Location Application: 120 to 277 Volt Voltage Rating; 1 Inch Diameter
Weight per unit	0.7200 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Beam Spread Angle	220 Degree
Glass Finish	FROSTED
Intensity	1800 LUMEN
Item	LED Tube
Voltage Rating	120 to 277 Volt
Wattage	15 Watt

Material, Color, and Finish

Base Type	G13 Medium 2-Pin
Color Rendering Index	80 A
Color Temperature in Kelvin	3500

Dimensions and Weight

Diameter	1 INCH
Length	47.5 Inch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120
75041-0000, TX Garland
Phone: 214-503-7227
Fax: 214-503-9766

Descriptions

Additional Information	RoHS Compliant; Shatter Proof Coated Glass; System Wattage 18.5 Watt; Efficacy 100 Lumen per Watt; Visible Light Area 325 Degree; Temperature -4 to 113 Deg F
Commodity Description	Led Linear Fluorescent Straight, U-Shape & Circular Lamps
Description	15W LED T8 48" 35K COMBO
extra long description	LINEAR, SINGLE ENDED, INSTANT START TYPE; 47.5 INCH; UL (CANADA AND US), UL, NSF/ANSI, DLC APPROVAL; FOOD EQUIPMENT, SPLASH ZONE, DRY AND DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1 INCH DIAMETER; 15 WATT WATTAGE; LED TUBE; G13 MEDIUM 2-PIN BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 1800 LUMEN INTENSITY; 3500; 80 COLOR RENDERING INDEX; FROSTED GLASS FINISH; 220 DEGREE BEAM SPREAD ANGLE; COMBODRIVE BRAND; ROHS COMPLIANT; SHATTER PROOF COATED GLASS; SYSTEM WATTAGE 18.5 WATT; EFFICA
Long Description	LINEAR FLUORESCENT LED LAMP, LINEAR, SINGLE ENDED, INSTANT START TYPE; 47.5 INCH; UL (CANADA AND US), UL, NSF/ANSI, DLC APPROVAL; FOOD EQUIPMENT, SPLASH ZONE, DRY AND DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1 INCH DIAMETER
Product Type	Linear Fluorescent Led Lamp

Manufacturer Information

Brand	Keystone Technologies
Manufacturers Part Number	KT-LED15T8-48GC-835-X
Model	800

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Linear, Single Ended, Instant Start

Packaging

Carton	25
Weight Per each	0.72

Uses, Certifications, and Standards

Application	Food Equipment, Splash Zone, Dry and Damp Location
Approval	UL (Canada and US), UL, NSF/ANSI, DLC