




GE
Lighting

90154 - GE LED PAR38

LED18DP38W827/25

 Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Lamp Type	LED-PAR
Primary Application	Indoor and outdoor Floodlight
Rated Life (Hours)	25000 h
Bulb Shape	PAR38

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	7000 cd
Lumens per Watt (Efficacy)	66.7 lm
Nominal Initial Lumen per Watt	67
Rated Beam Spread	25 rad
Initial Lumens-nominal	1200 lm
Color Rendering Index-CRI	84
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	90154
Description	LED18DP38W827/25
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	18 W