




KT-LEDXXA21-O-E26-8XX

REPLACEMENT LAMP

Enclosed
Fixture Rated**5 YEAR**
WARRANTY

DESCRIPTION

14–20W Commercial A21 Lamp | 2700–5000K | > 80 CRI | Omni-Directional

LAMP TYPE: Commercial A21**BASE TYPE:** E26 (Medium)**WATTAGE:** 14–20W**COLOR TEMPERATURE:** 2700–5000K**COLOR RENDERING INDEX (CRI):** > 80**WARRANTY:** 5 Years

PRODUCT FEATURES

- Up to 75% energy saving compared to legacy equivalent lamps
- Can be used in base-up or base-down position
- Rated for open and enclosed fixtures
- Large metal heatsink for optimal heat dissipation
- THD < 20%
- PF > 0.90
- Operating temperature range –4°F/–20°C to 113°F/45°C; 95°F/35°C max for fully enclosed fixture
- Ideal for post top, bollards, and outdoor corridor lighting
- Suitable for dry and damp location
- 1598C Rated pending

PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Base Type	Rated Lamp Wattage	Legacy Equivalent Wattage	Color Temp	Lumens	Efficacy	Input Voltage	CRI	Beam Angle	Dimmable
KT-LED14A21-O-E26-827	E26	14W	100W incandescent	2700K	1764	126 lm/W	120–277V	> 80	340°	No
KT-LED14A21-O-E26-830	E26	14W	100W incandescent	3000K	1792	128 lm/W	120–277V	> 80	340°	No
KT-LED14A21-O-E26-840	E26	14W	100W incandescent	4000K	1918	137 lm/W	120–277V	> 80	340°	No
KT-LED14A21-O-E26-850	E26	14W	100W incandescent	5000K	1960	140 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-827	E26	20W	150W incandescent	2700K	2500	125 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-830	E26	20W	150W incandescent	3000K	2620	131 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-840	E26	20W	150W incandescent	4000K	2720	136 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-850	E26	20W	150W incandescent	5000K	2740	137 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-827-DIM	E26	20W	150W incandescent	2700K	2460	123 lm/W	120V	> 80	340°	Yes
KT-LED20A21-O-E26-830-DIM	E26	20W	150W incandescent	3000K	2500	125 lm/W	120V	> 80	340°	Yes
KT-LED20A21-O-E26-840-DIM	E26	20W	150W incandescent	4000K	2620	131 lm/W	120V	> 80	340°	Yes
KT-LED20A21-O-E26-850-DIM	E26	20W	150W incandescent	5000K	2660	133 lm/W	120V	> 80	340°	Yes


KT-LEDXXA21-O-E26-8XX

REPLACEMENT LAMP

PHOTOMETRIC SPECIFICATIONS


LUMINOUS INTENSITY DISTRIBUTION

KT-LED14A21-O-E26-850




C Plane	50% MaxAng.	10% MaxAng.
■ C0.0_180.0	289.6	339.2
■ C90.0_270.0	291.1	339.5

KT-LED20A21-O-E26-850




C Plane	50% MaxAng.	10% MaxAng.
■ C0.0_180.0	281.1	336.7
■ C90.0_270.0	283.1	337.3

KT-LED20A21-O-E26-850-DIM



C Plane	50% MaxAng.	10% MaxAng.
■ C0.0_180.0	284.6	339.4
■ C90.0_270.0	285.6	338.9

PHYSICAL SPECIFICATIONS



LAMP DIMENSIONS

A (Length)	5.26"
B (Diameter)	2.56"

BASE TYPE: E26 (Medium)

PACKAGING

Carton Quantity	24 pcs
Carton Dimensions	11.6" × 13.38" × 15"
Carton Weight	19.1 lbs



KT-LEDXXA21-O-E26-8XX

REPLACEMENT LAMP

ORDERING INFORMATION

CATALOG NUMBER	EASY CODE	UPC
KT-LED14A21-O-E26-827	MKD-50	843654122700
KT-LED14A21-O-E26-830	LTE-35	843654122717
KT-LED14A21-O-E26-840	XEF-64	843654122724
KT-LED14A21-O-E26-850	XOI-75	843654122731
KT-LED20A21-O-E26-827	GAU-17	843654122748
KT-LED20A21-O-E26-830	SXF-69	843654122755
KT-LED20A21-O-E26-840	OPF-90	843654122762
KT-LED20A21-O-E26-850	XJH-40	843654122779
KT-LED20A21-O-E26-827-DIM	CLA-73	843654122786
KT-LED20A21-O-E26-830-DIM	JRC-19	843654122793
KT-LED20A21-O-E26-840-DIM	TMJ-80	843654122809
KT-LED20A21-O-E26-850-DIM	QHI-50	843654122816

CATALOG NUMBER BREAKDOWN

KT-LEDXXA21-O-E26-8XX

1 2 3 4 5 6 7 8

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 Omni-Directional
- 6 Base Type
- 7 80 CRI
- 8 CCT



KT-LEDXXA21-O-E26-8XX

REPLACEMENT LAMP

DESCRIPTION

14–20W Commercial A21 Lamp | 2700–5000K | > 80 CRI | Omni-Directional




Enclosed
Fixture Rated

RoHS
Compliant



5 YEAR
WARRANTY



LAMP TYPE: Commercial A21

BASE TYPE: E26 (Medium)

WATTAGE: 14–20W

COLOR TEMPERATURE: 2700–5000K

COLOR RENDERING INDEX (CRI): > 80

WARRANTY: 5 Years

PRODUCT FEATURES

- Up to 75% energy saving compared to legacy equivalent lamps
- Can be used in base-up or base-down position
- Rated for open and enclosed fixtures
- Large metal heatsink for optimal heat dissipation
- THD < 20%
- PF > 0.90
- Operating temperature range –4°F/–20°C to 113°F/45°C; 95°F/35°C max for fully enclosed fixture
- Ideal for post top, bollards, and outdoor corridor lighting
- Suitable for dry and damp location
- 1598C Rated pending

PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Base Type	Rated Lamp Wattage	Legacy Equivalent Wattage	Color Temp	Lumens	Efficacy	Input Voltage	CRI	Beam Angle	Dimmable
KT-LED14A21-O-E26-827	E26	14W	100W incandescent	2700K	1764	126 lm/W	120–277V	> 80	340°	No
KT-LED14A21-O-E26-830	E26	14W	100W incandescent	3000K	1792	128 lm/W	120–277V	> 80	340°	No
KT-LED14A21-O-E26-840	E26	14W	100W incandescent	4000K	1918	137 lm/W	120–277V	> 80	340°	No
KT-LED14A21-O-E26-850	E26	14W	100W incandescent	5000K	1960	140 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-827	E26	20W	150W incandescent	2700K	2500	125 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-830	E26	20W	150W incandescent	3000K	2620	131 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-840	E26	20W	150W incandescent	4000K	2720	136 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-850	E26	20W	150W incandescent	5000K	2740	137 lm/W	120–277V	> 80	340°	No
KT-LED20A21-O-E26-827-DIM	E26	20W	150W incandescent	2700K	2460	123 lm/W	120V	> 80	340°	Yes
KT-LED20A21-O-E26-830-DIM	E26	20W	150W incandescent	3000K	2500	125 lm/W	120V	> 80	340°	Yes
KT-LED20A21-O-E26-840-DIM	E26	20W	150W incandescent	4000K	2620	131 lm/W	120V	> 80	340°	Yes
KT-LED20A21-O-E26-850-DIM	E26	20W	150W incandescent	5000K	2660	133 lm/W	120V	> 80	340°	Yes


KT-LEDXXA21-O-E26-8XX

REPLACEMENT LAMP

PHOTOMETRIC SPECIFICATIONS


LUMINOUS INTENSITY DISTRIBUTION

KT-LED14A21-O-E26-850




C Plane	50% MaxAng.	10% MaxAng.
■ C0.0_180.0	289.6	339.2
■ C90.0_270.0	291.1	339.5

KT-LED20A21-O-E26-850




C Plane	50% MaxAng.	10% MaxAng.
■ C0.0_180.0	281.1	336.7
■ C90.0_270.0	283.1	337.3

KT-LED20A21-O-E26-850-DIM



C Plane	50% MaxAng.	10% MaxAng.
■ C0.0_180.0	284.6	339.4
■ C90.0_270.0	285.6	338.9

PHYSICAL SPECIFICATIONS



LAMP DIMENSIONS

A (Length)	5.26"
B (Diameter)	2.56"

BASE TYPE: E26 (Medium)

PACKAGING

Carton Quantity	24 pcs
Carton Dimensions	11.6" × 13.38" × 15"
Carton Weight	19.1 lbs



KT-LEDXXA21-O-E26-8XX

REPLACEMENT LAMP

ORDERING INFORMATION

CATALOG NUMBER	EASY CODE	UPC
KT-LED14A21-O-E26-827	MKD-50	843654122700
KT-LED14A21-O-E26-830	LTE-35	843654122717
KT-LED14A21-O-E26-840	XEF-64	843654122724
KT-LED14A21-O-E26-850	XOI-75	843654122731
KT-LED20A21-O-E26-827	GAU-17	843654122748
KT-LED20A21-O-E26-830	SXF-69	843654122755
KT-LED20A21-O-E26-840	OPF-90	843654122762
KT-LED20A21-O-E26-850	XJH-40	843654122779
KT-LED20A21-O-E26-827-DIM	CLA-73	843654122786
KT-LED20A21-O-E26-830-DIM	JRC-19	843654122793
KT-LED20A21-O-E26-840-DIM	TMJ-80	843654122809
KT-LED20A21-O-E26-850-DIM	QHI-50	843654122816

CATALOG NUMBER BREAKDOWN

KT-LEDXXA21-O-E26-8XX

1 2 3 4 5 6 7 8

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 Omni-Directional
- 6 Base Type
- 7 80 CRI
- 8 CCT