SINCE 1945
KEYSTONE
LIGHT MADE EASY

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9BR30-8XX
REPLACEMENT LAMP

DESCRIPTION
9W BR30 Lamp | 2700–5000K | >80 CRI | Standard Flood

c UL us LISTED · RoHS Compliant · 3 YEAR WARRANTY

- **LAMP TYPE:** BR30
- **BASE TYPE:** E26 (Medium)
- **WATTAGE:** 9W
- **COLOR TEMPERATURE:** 2700–5000K
- **COLOR RENDERING INDEX (CRI):** >80
- **WARRANTY:** 3 Years
- **RATED LIFE:** L70 (15,000 Hours)



TYPICAL APPLICATIONS
- Recessed downlights
- Track lighting
- Surface-mount ceiling fixtures

PRODUCT FEATURES
- Energy efficient, 80%+ energy savings over legacy equivalents
- Lower heat generation than legacy equivalents
- Smooth, uniform dimming
- Smooth, diffused lens for comfortable glare-free performance
- Durable plastic housing lowers the risk for breakage
- Long life minimizes replacement and maintenance costs
- Suitable for use in damp locations
- Operating temperature range –4°F/–20°C to 95°F/35°C
- PF >0.70
- ANSI compliant construction ensures fitment for intended applications
- UL Listed
- Complies with Part 15 of FCC

ELECTRICAL AND PERFORMANCE SPECIFICATIONS


Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED9BR30-827	BR30 bulb; Standard flood; Dimmable	2700K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W
KT-LED9BR30-830	BR30 bulb; Standard flood; Dimmable	3000K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W
KT-LED9BR30-835	BR30 bulb; Standard flood; Dimmable	3500K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W
KT-LED9BR30-840	BR30 bulb; Standard flood; Dimmable	4000K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W
KT-LED9BR30-850	BR30 bulb; Standard flood; Dimmable	5000K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W

SINCE 1945
KEYSTONE
LIGHT MADE EASY

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9BR30-8XX
REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



LAMP DIMENSIONS

A (Diameter)	3.78"
B (Length)	5.28"

BASE TYPE: E26 (Medium)

PACKAGING

Carton Quantity	24 pcs
Carton Dimensions	15.91" × 12.05" × 12.13"
Carton Weight	8.9 lbs

ORDERING INFORMATION

ORDER CODE	CARTON QUANTITY	EASY CODE	UPC
KT-LED9BR30-827	24 pcs	NKS-70	843654125978
KT-LED9BR30-830	24 pcs	DTG-25	843654125992
KT-LED9BR30-835	24 pcs	IJB-34	843654127576
KT-LED9BR30-840	24 pcs	MXB-89	843654126012
KT-LED9BR30-850	24 pcs	GMP-50	843654126029

CATALOG NUMBER BREAKDOWN

KT-LED9BR30-8XX

1 2 3 4 5 6

1 **Keystone Technologies**
2 **LED Lamp**
3 **Wattage**
4 **Lamp Shape**
5 **800 Series**
6 **Color Temperature**

SINCE 1945
KEYSTONE
LIGHT MADE EASY

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9BR30-8XX
REPLACEMENT LAMP

DESCRIPTION
9W BR30 Lamp | 2700–5000K | >80 CRI | Standard Flood

c UL us LISTED · RoHS Compliant · 3 YEAR WARRANTY

- **LAMP TYPE:** BR30
- **BASE TYPE:** E26 (Medium)
- **WATTAGE:** 9W
- **COLOR TEMPERATURE:** 2700–5000K
- **COLOR RENDERING INDEX (CRI):** >80
- **WARRANTY:** 3 Years
- **RATED LIFE:** L70 (15,000 Hours)



TYPICAL APPLICATIONS
- Recessed downlights
- Track lighting
- Surface-mount ceiling fixtures

PRODUCT FEATURES
- Energy efficient, 80%+ energy savings over legacy equivalents
- Lower heat generation than legacy equivalents
- Smooth, uniform dimming
- Smooth, diffused lens for comfortable glare-free performance
- Durable plastic housing lowers the risk for breakage
- Long life minimizes replacement and maintenance costs
- Suitable for use in damp locations
- Operating temperature range –4°F/–20°C to 95°F/35°C
- PF >0.70
- ANSI compliant construction ensures fitment for intended applications
- UL Listed
- Complies with Part 15 of FCC

ELECTRICAL AND PERFORMANCE SPECIFICATIONS


Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED9BR30-827	BR30 bulb; Standard flood; Dimmable	2700K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W
KT-LED9BR30-830	BR30 bulb; Standard flood; Dimmable	3000K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W
KT-LED9BR30-835	BR30 bulb; Standard flood; Dimmable	3500K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W
KT-LED9BR30-840	BR30 bulb; Standard flood; Dimmable	4000K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W
KT-LED9BR30-850	BR30 bulb; Standard flood; Dimmable	5000K	120V	9W	65W halogen	E26	650 lm	>80	120°	Yes	72 lm/W

SINCE 1945
KEYSTONE
LIGHT MADE EASY

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED9BR30-8XX
REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



LAMP DIMENSIONS

A (Diameter)	3.78"
B (Length)	5.28"

BASE TYPE: E26 (Medium)

PACKAGING

Carton Quantity	24 pcs
Carton Dimensions	15.91" × 12.05" × 12.13"
Carton Weight	8.9 lbs

ORDERING INFORMATION

ORDER CODE	CARTON QUANTITY	EASY CODE	UPC
KT-LED9BR30-827	24 pcs	NKS-70	843654125978
KT-LED9BR30-830	24 pcs	DTG-25	843654125992
KT-LED9BR30-835	24 pcs	IJB-34	843654127576
KT-LED9BR30-840	24 pcs	MXB-89	843654126012
KT-LED9BR30-850	24 pcs	GMP-50	843654126029

CATALOG NUMBER BREAKDOWN

KT-LED9BR30-8XX

1 2 3 4 5 6

1 **Keystone Technologies**
2 **LED Lamp**
3 **Wattage**
4 **Lamp Shape**
5 **800 Series**
6 **Color Temperature**