

## FEATURES & SPECIFICATIONS

### PRODUCT OVERVIEW

Ideal for commercial or residential landscape, sign or façade applications.

### CONSTRUCTION

Rugged, die-cast aluminum housing. Landscape post is constructed of heavy wall extruded aluminum.

Adjustable mounting knuckle with 1/2" NPS threaded stem. Mounting post provides a stable platform for ease of installation.

### LISTING

Listed and labeled to UL standards for wet locations.

Listed and labeled to CSA standards.

### WARRANTY

2-year limited warranty. Complete warranty terms located at:

[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

Note: Actual performance may differ as a result of end-user environment and application.

Specifications subject to change without notice.

Catalog Number
Notes
Type

Contractor Select


# Landscape Lighting




### ORDERING INFORMATION

Catalog Number	UPC	Description	Max Wattage	Lamp Source	Voltage	Finish	Lamp Included	Approx. Weight (lbs)	Pallet Qty	Standard Carton Qty
FB50IW M12	745973817957	Par20 bullet flood	50	Incandescent	120	White	N	1	576	12
FB150I M12	745973818046	Par38 bullet flood	150	Incandescent	120	Black	N	2	192	12
FB150IG M12	745973818053	Par38 bullet flood	150	Incandescent	120	Green	N	2	192	12
FB150IW M12	745973818077	Par38 bullet flood	150	Incandescent	120	White	N	2	192	12
LT60IG M12	745974380641	Tiered pagoda	60	Incandescent	120	Green	N	1	144	12
LFP M6	745973818107	Landscape post	--	--	--	Green	--	2	288	6


# Landscape Lighting




**FB50**



**FB150**



**LT60**



**LFP**

All dimensions are inches (centimeters).