

# Specifications

## Eaton LR67 SA



Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, LR shape, 2"

### General specifications

|                                 |                                                                     |
|---------------------------------|---------------------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Crouse-Hinds series<br>Condulet Form 7 conduit<br>outlet body |
| <b>CATALOG NUMBER</b>           | LR67 SA                                                             |
| <b>UPC</b>                      | 782274529318                                                        |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 8.13 in                                                             |
| <b>PRODUCT HEIGHT</b>           | 4.13 in                                                             |
| <b>PRODUCT WIDTH</b>            | 3.13 in                                                             |
| <b>PRODUCT WEIGHT</b>           | 1.9 lb                                                              |

Photo is representative



## Certifications and compliances

|                     |                                  |
|---------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE      | NEC/CEC                          |
| NEMA RATING         | 12                               |

## Product specifications

|            |                      |
|------------|----------------------|
| SHAPE      | LR                   |
| TRADE SIZE | 2"                   |
| MATERIAL   | Copper-free aluminum |

## Resources

CATALOGS [Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS [Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)  
[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

INSTALLATION INSTRUCTIONS [IF 964 - Conduit Body Wire Pulling](#)  
[IF 863 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - LR67 SA](#)  
[Condulet Form 7 Industrial Grade Conduit Bodies](#)

TECHNICAL SERVICE BULLETINS [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)  
[Industrial Fittings Wire Fill Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton LR67 SA



Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, LR shape, 2"

### General specifications

|                     |                                                                     |
|---------------------|---------------------------------------------------------------------|
| <b>PRODUCT NAME</b> | Eaton Crouse-Hinds series<br>Condulet Form 7 conduit<br>outlet body |
|---------------------|---------------------------------------------------------------------|

|                       |         |
|-----------------------|---------|
| <b>CATALOG NUMBER</b> | LR67 SA |
|-----------------------|---------|

|            |              |
|------------|--------------|
| <b>UPC</b> | 782274529318 |
|------------|--------------|

|                                 |         |
|---------------------------------|---------|
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 8.13 in |
|---------------------------------|---------|

|                       |         |
|-----------------------|---------|
| <b>PRODUCT HEIGHT</b> | 4.13 in |
|-----------------------|---------|

|                      |         |
|----------------------|---------|
| <b>PRODUCT WIDTH</b> | 3.13 in |
|----------------------|---------|

|                       |        |
|-----------------------|--------|
| <b>PRODUCT WEIGHT</b> | 1.9 lb |
|-----------------------|--------|

Photo is representative



Powering Business Worldwide

## Certifications and compliances

|                     |                                  |
|---------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE      | NEC/CEC                          |
| NEMA RATING         | 12                               |

## Product specifications

|            |                      |
|------------|----------------------|
| SHAPE      | LR                   |
| TRADE SIZE | 2"                   |
| MATERIAL   | Copper-free aluminum |

## Resources

**CATALOGS** [Crouse-Hinds series Form 7 catalog page](#)

**CERTIFICATION REPORTS** [Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)  
[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

**INSTALLATION INSTRUCTIONS** [IF 964 - Conduit Body Wire Pulling](#)  
[IF 863 - Conduit Body Wire Pulling](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - LR67 SA](#)  
[Condulet Form 7 Industrial Grade Conduit Bodies](#)

**TECHNICAL SERVICE BULLETINS** [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)  
[Industrial Fittings Wire Fill Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

