



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT38NM 3/8" N/M LT 100' Coil *Southwire Company*

Catalog Number	LT38NM
Manufacturer	Southwire Company
Description	UI Liquidtight Flexible Nonmetallic Conduit, Type LFNC-B, 6000 Series, Liquidtight Flexible Nonmetallic Conduit. Rugged Sunlight and Oil Resistant PVC Construction . Color: Gray, 3/8 Inch Diameter, 100 Foot Carton
Weight per unit	0.1100 (lbs/each)
Product Category	19980511081033

Features

Inside Diameter	0.484/0.504
Material	PVC
outside diameter	0.690/0.710

Material, Color, and Finish

Color	Gray
Finish	PVC
Jacket Material	PVC

Dimensions and Weight

Diameter	3/8"
Length	100



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Also Known As...	Liquid Tight Conduit Carflex®
Description	3/8" N/M LT 100' COIL
extra long description	AFC 6001-30-00 3/8 LIQUID TUFF NMLT
Features	Liquidtight Flexible Non-Metallic conduit is a versatile product that has a variety of applications for indoor and outdoor locations. Non-metallic conduit is used in fixture whips, data centers, electric signs and outdoor lighting, HVAC, pool and spas and locations with exposure to sunlight and weather conditions and more. Our non-metallic conduit has a rigid PVC core for strength and is rated for concrete embedment. Our non-metallic conduit Type LFNC-B is available in long length reels in sizes 1/2" to 1"
Long Description	UL Liquidtight Flexible Nonmetallic Conduit, Type LFNC-B, 6000 Series, Liquidtight Flexible Nonmetallic Conduit. Rugged Sunlight and Oil Resistant PVC Construction . Color: Gray, 3/8 inch Diameter, 100 Foot Carton
Product Type	3/8 Liquid Tuff NMLT 100 CTN
Short Description	3/8 LIQUID TUFF NMLT 100 CTN
similar brands	Sealtite®
Special Features	Rugged non-metallic PVC; Interior integral reinforced member within conduit wall; Integral Type B construction per NEC 356.2(2); Rigid PVC spiral core for strength; Outdoor applications including direct burial; Rated for concrete embedment; Sunlight and oil resistant; Non-conductive raceway; For lower potential circuits; Rated for direct burial and poured concrete; Hazardous locations per NEC 501; Industrial and commercial applications; Indoor or outdoor locations; Suitable for pool and spa use

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680136275
Manufacturers Part Number	6001-30-00
UPC	077680136275

Taxonomies, Classifications, and Categories

Category Description	NON-METALLIC SEALTITE AND FITTINGS
Type	Liquidtight Flexible Non-Metallic Conduit

Trade Size

Trade Size	3/8
------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Weight	0.12
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Industrial and commercial applications; Indoor or outdoor locations; Suitable for pool and spa use. For Air Conditioning And HVAC Units.
Temperature Rating	176