



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## M22 Modular Selector Switch Operator

M22S-WKV

UPC:786685280820

### Dimensions:

- **Height:** 1.06 IN
- **Length:** 1.17 IN
- **Width:** 1.17 IN

**Weight:** .995 LB

**Notes:** Includes contact block mounting adapter.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Selector switch
- **Action:** Maintained V
- **Actuator:** Knob
- **Bezel:** Black
- **Environmental Rating:** IP66, NEMA 4X, 13
- **Illumination:** Non-illuminated
- **Number Of Positions:** Two-position, V
- **Operating Cycles:** 100,000 operations
- **Size:** 22.5 mm
- **Series:** M22

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [M22\(S\)\(M\)-WKV 3D Model Xchange](#)
- [M22\(S\)\(M\)-WKV AutoCAD 2D Footprint \(mm\)](#)
- [M22\(S\)\(M\)-WKV 2D Drawing Xchange](#)
- [M22\(S\)\(M\)-WKV 2D PDF](#)
- [M22\(S\)\(M\)-WKV AutoCAD 2D Footprint](#)



- [M22\(S\)\(M\)-WKV 3D Inventor](#)
- [M22 Pilot Devices](#)
- [Eaton Specification Sheet - M22S-WKV](#)
- [Global Data Sheet - M22S-WKV](#)

**Certifications:**

- CCC Marked
- CSA Certified
- Lloyd's Register Certified

**Product compliance:**

- Bureau Veritas
- GoST-R
- CE Marked



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## M22 Modular Selector Switch Operator

M22S-WKV

UPC:786685280820

### Dimensions:

- **Height:** 1.06 IN
- **Length:** 1.17 IN
- **Width:** 1.17 IN

**Weight:** .995 LB

**Notes:** Includes contact block mounting adapter.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Selector switch
- **Action:** Maintained V
- **Actuator:** Knob
- **Bezel:** Black
- **Environmental Rating:** IP66, NEMA 4X, 13
- **Illumination:** Non-illuminated
- **Number Of Positions:** Two-position, V
- **Operating Cycles:** 100,000 operations
- **Size:** 22.5 mm
- **Series:** M22

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [M22\(S\)\(M\)-WKV 3D Model Xchange](#)
- [M22\(S\)\(M\)-WKV AutoCAD 2D Footprint \(mm\)](#)
- [M22\(S\)\(M\)-WKV 2D Drawing Xchange](#)
- [M22\(S\)\(M\)-WKV 2D PDF](#)
- [M22\(S\)\(M\)-WKV AutoCAD 2D Footprint](#)



- [M22\(S\)\(M\)-WKV 3D Inventor](#)
- [M22 Pilot Devices](#)
- [Eaton Specification Sheet - M22S-WKV](#)
- [Global Data Sheet - M22S-WKV](#)

**Certifications:**

- CCC Marked
- CSA Certified
- Lloyd's Register Certified

**Product compliance:**

- Bureau Veritas
- GoST-R
- CE Marked