

Eaton MBT48B200BTS

Catalog Number: MBT48B200BTS

Eaton resi meter breaker, All-in-ones, 200A, C, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm22 kAIC, #6-350 kcmCSR2200, Surface mounting, 8, Four-jaw, 1, 4, Single-phase, Ringless, Used with BR breakers, 120/240 Vac



General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MBT48B200BTS
UPC	Product Length/Depth
782116157372	4.94 in
Product Height	Product Width
25.5 in	14.44 in
Product Weight	Warranty
33.05 lb	10 year
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

AL : Alabama Power

ME : Central Maine Power

MO : Empire District Electric

OK : Empire District Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

MD : First Energy (Potomac Edison)

VA : First Energy (Potomac Edison)

WV : First Energy (Mon Power)

NJ : First Energy (Jersey Central Power and Light)

OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company)

PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power)

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

NY : Rochester Gas & Electric (RG&E)

NC : Dominion

VA : Dominion

Interrupt rating

10 kAIC

Box size

C

Enclosure

NEMA 3R

Ground

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - METER BREAKER TRAILER PANEL](#)

Specifications and datasheets

[Eaton Specification Sheet - MBT48B200BTS](#)

#6-350 kcmil

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Number of circuits

8

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR2200

Number of jaws

Four-jaw



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia