



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Time-Delay Fuse

**MDL-20**

**UPC:**051712724593

**Dimensions:**

- **Height:** .25 IN
- **Length:** 1.25 IN
- **Width:** .25 IN

**Weight:**.006 LB

**Warranties:**

- Not Applicable

**Specifications:**

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 20A
- **Voltage Rating:** 32 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 1 kAIC at 32 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Response Time:** 60 min maximum at 135%,  
120 s maximum at 200%, 5 s minimum at 200%
- **Material:** Glass tube with nickel plated brass  
endcap
- **Connection:** Ferrule end X ferrule end

**Supporting documents:**

- [BUSS SMALL DIMENSION Fuse](#)

**Certifications:** No Data

**Product compliance:**

- CE Marked





Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Time-Delay Fuse

**MDL-20**

**UPC:**051712724593

**Dimensions:**

- **Height:** .25 IN
- **Length:** 1.25 IN
- **Width:** .25 IN

**Weight:**.006 LB

**Warranties:**

- Not Applicable

**Specifications:**

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 20A
- **Voltage Rating:** 32 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 1 kAIC at 32 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Response Time:** 60 min maximum at 135%,  
120 s maximum at 200%, 5 s minimum at 200%
- **Material:** Glass tube with nickel plated brass  
endcap
- **Connection:** Ferrule end X ferrule end

**Supporting documents:**

- [BUSS SMALL DIMENSION Fuse](#)

**Certifications:** No Data

**Product compliance:**

- CE Marked

