



MDL25 25A 32V TD Glass Fuse

Bussmann Fuses

Catalog Number	MDL25
Manufacturer	Bussmann Fuses
Description	Eaton MDL Series Time-Delay Fuse 25A, 32 Vac, Non-Indicating
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	25
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
interrupt rating	1 kAIC at 32 Vac
Material	Glass FuseNickel-plated brass end cap construction
Response Time	60 min at 135%, 120 sec at 200%, 5 sec at 200%
Voltage Rating	32 Vac, 32 Vdc (self certified)

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	25A 32V TD GLASS FUSE
extra long description	EFSE MDL-25 1/4" X 1-1/4" TIME DELA
Features	Eaton's Bussmann Division develops and manufactures critical circuit protection, power management and electrical safety products designed to provide innovative circuit and power electronics protection, serving the commercial, data center, electrical vehicle, food and beverage, and other markets.
Long Description	Eaton MDL Series Time-delay fuse 25A, 32 Vac, Non-indicating
Product Type	1/4" X 1-1/4" Time Delay Glass - 25 Amp
Special Features	Interrupt Rating 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712724609
Manufacturers Part Number	MDL-25
UPC	051712724609

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Time-delay fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	0.01

Uses, Certifications, and Standards

Application standard	Ind Facilities & Factories - Facility: Safety and Security Systems CE Marked
----------------------	---