




NON-METALLIC LOW PROFILE WIU COVERS

**Single Gang Flat Expandable While-In-Use Covers
Horizontal/Vertical 16-in-1**

C07



Catalog #: ML450G

APPLICATIONS

Low profile design that is expandable for weatherproof protection while an outlet is in use.
N/A

PRODUCT FEATURES

Revolutionary patented design expands from 1" to 3" for while-in-use needs
100% paintable surface
Ultra rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
Includes attached gasket and mounting hardware

UL LISTED

File E116141

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

US PATENTS

8,101,861; 8,319,334; 8,053,671

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Gangs: 1

PRODUCT MEASUREMENTS

Depth: 1 in. to 3 in.
Wt. Ea. (Lbs.): 0.410

PACKAGING

Package Type: Shrink
Std. Pkg.: 10
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 41.00
Ship Carton Length (in.): 13.13
Ship Carton Width (in.): 4.38
Ship Carton Height (in.): 6.63
Ctn Weight (Lbs.): 4.10
Pallet Qty: 1800.00
UPC Number: 092326111867
I2of5: 30092326111868