




NON-METALLIC LOW PROFILE WIU COVERS

Single Gang Flat Expandable While-In-Use Covers - Extra Duty®
Horizontal/Vertical 16-in-1

C07.1



Catalog #: ML500G

APPLICATIONS

Low profile design that is expandable for weatherproof protection while an outlet is in use.

PRODUCT FEATURES

- Revolutionary patented design expands from 1" to 3" for while-in-use needs
- 100% paintable surface
- Ultra rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Includes attached gasket and mounting hardware

UL LISTED

File E116141

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A & B) Extra Duty Rated

US PATENTS

8,101,861; 8,319,334; 8,053,671

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Gangs: 1

PRODUCT MEASUREMENTS

Depth: 1 in. to 3 in.
Wt. Ea. (Lbs.): 0.410

PACKAGING

Package Type: Shrink
 Std. Pkg.: 10
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 41.00
 Ship Carton Length (in.): 13.13
 Ship Carton Width (in.): 4.38
 Ship Carton Height (in.): 6.63
 Ctn Weight (Lbs.): 4.10
 Pallet Qty: 1800.00
 UPC Number: 050169917411
 I2of5: 50050169917416