



TWO GANG WIU COVERS

**Two Gang - While In use Covers - Extra Duty®
2-Gang 55-in-1**

C05.1



Catalog #: MM2420C

APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use.
N/A

PRODUCT FEATURES

- High-impact polycarbonate construction provides maximum durability
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Includes attached gasket and mounting hardware
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Lockable tab

UL LISTED

File E116141

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A & B) Extra Duty Rated

US PATENTS

8,314,335

GENERAL PRODUCT INFORMATION

Color:	Clear
Country of Origin:	USA

CONFIGURATION

Gangs:	2
--------	---

PRODUCT MEASUREMENTS

Depth:	2-3/4 in.
Wt. Ea. (Lbs.):	0.700

PACKAGING

Package Type:	Shrink
Std. Pkg.:	6
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	70.00
Ship Carton Length (in.):	19.50
Ship Carton Width (in.):	5.56
Ship Carton Height (in.):	6.00
Ctn Weight (Lbs.):	4.20
Pallet Qty:	504.00
UPC Number:	050169917305
I2of5:	50050169917300